

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268055

Luminaire Tested: P3A18R129735D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A18R129735D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 625.0 lumens
Efficiency: N/A
Efficacy: 27.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268055

CATALOG NUMBER: P3A18R129735D010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1268055

CATALOG NUMBER: P3A18R129735D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269518
5°	249086
10°	198861
15°	150217
20°	114390
25°	87174
30°	62440
35°	40743
40°	24990
45°	15102
50°	10030
55°	7761
60°	6666
65°	5811
70°	5193
75°	5168
80°	3788
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15102 cd/sqm

TEST NUMBER: P1268055

CATALOG NUMBER: P3A18R129735D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	16.0
10°-20°	185.0	29.6
20°-30°	164.7	26.3
30°-40°	97.4	15.6
40°-50°	40.0	6.4
50°-60°	18.8	3.0
60°-70°	11.4	1.8
70°-80°	6.0	1.0
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	449.9	72.0
0°-40°	547.3	87.6
0°-60°	606.1	97.0
0°-90°	625.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	625.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1229	
5°	1132	100
15°	662	185
25°	360	165
35°	152	97
45°	49	40
55°	20	19
65°	11	11
75°	6	6
85°	1	1
90°	0	

TEST NUMBER: P1268055

CATALOG NUMBER: P3A18R129735D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1229.1
1°	1226.0
2°	1216.9
3°	1198.6
4°	1168.2
5°	1131.6
6°	1092.1
7°	1045.4
8°	996.7
9°	946.9
10°	893.1
12.5°	770.3
15°	661.7
17.5°	568.4
20°	490.2
22.5°	421.2
25°	360.3
27.5°	301.4
30°	246.6
32.5°	196.9
35°	152.2
37.5°	116.7
40°	87.3
42.5°	65.0
45°	48.7
47.5°	37.6
50°	29.4
52.5°	24.4
55°	20.3
57.5°	17.3
60°	15.2
62.5°	13.2
65°	11.2
67.5°	10.1
70°	8.1
72.5°	7.1
75°	6.1
77.5°	4.1
80°	3.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)