

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268068

Luminaire Tested: P3A20R159735D010 E3D1LI

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1268068  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R159735D010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2036.0 lumens  
Efficiency: N/A  
Efficacy: 70.7 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268068

CATALOG NUMBER: P3A20R159735D010 E3D1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1268068

CATALOG NUMBER: P3A20R159735D010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 |  | 104 | 103 | 102 |  | 101 |
| 2   | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 |  | 102 | 100 | 99  |  | 99  |
| 3   | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99  | 102 | 100 | 98  |  | 100 | 98  | 96  |  | 98  |
| 4   | 107 | 102 | 99  | 96  | 105 | 101 | 98  | 96  | 99  | 97  | 95  |  | 98  | 96  | 94  |  | 96  |
| 5   | 105 | 100 | 96  | 94  | 103 | 99  | 96  | 93  | 97  | 94  | 92  |  | 96  | 93  | 92  |  | 94  |
| 6   | 102 | 97  | 94  | 91  | 101 | 96  | 93  | 91  | 95  | 92  | 90  |  | 94  | 92  | 90  |  | 93  |
| 7   | 100 | 95  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 88  |  | 92  | 90  | 88  |  | 91  |
| 8   | 98  | 93  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 89  | 87  |  | 91  | 88  | 86  |  | 90  |
| 9   | 96  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  |  | 89  | 87  | 85  |  | 89  |
| 10  | 95  | 89  | 86  | 84  | 94  | 89  | 86  | 84  | 88  | 85  | 83  |  | 88  | 85  | 83  |  | 87  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 3877080 |
| 5°  | 3161493 |
| 10° | 1548312 |
| 15° | 473896  |
| 20° | 200684  |
| 25° | 90779   |
| 30° | 35373   |
| 35° | 16329   |
| 40° | 5095    |
| 45° | 1923    |
| 50° | 785     |
| 55° | 306     |
| 60° | 351     |
| 65° | 415     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1923 cd/sqm

TEST NUMBER: P1268068

CATALOG NUMBER: P3A20R159735D010 E3D1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1118.0 | 54.9      |
| 10°-20°   | 686.0  | 33.7      |
| 20°-30°   | 184.3  | 9.0       |
| 30°-40°   | 40.6   | 2.0       |
| 40°-50°   | 5.7    | 0.3       |
| 50°-60°   | 1.0    | 0.1       |
| 60°-70°   | 0.5    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1988.2 | 97.7      |
| 0°-40°    | 2028.8 | 99.6      |
| 0°-60°    | 2035.5 | 100.0     |
| 0°-90°    | 2036.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2036.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 17681 |      |
| 5°  | 14363 | ###  |
| 15° | 2088  | 686  |
| 25° | 375   | 184  |
| 35° | 61    | 41   |
| 45° | 6     | 6    |
| 55° | 1     | 1    |
| 65° | 1     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1268068

CATALOG NUMBER: P3A20R159735D010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 17680.9 |
| 1°    | 17570.5 |
| 2°    | 17216.1 |
| 3°    | 16577.6 |
| 4°    | 15616.5 |
| 5°    | 14362.7 |
| 6°    | 12944.5 |
| 7°    | 11364.9 |
| 8°    | 9913.5  |
| 9°    | 8374.9  |
| 10°   | 6953.6  |
| 11°   | 5547.0  |
| 12°   | 4267.7  |
| 13°   | 3282.6  |
| 14°   | 2598.6  |
| 15°   | 2087.5  |
| 17.5° | 1293.9  |
| 20°   | 860.0   |
| 22.5° | 579.0   |
| 25°   | 375.2   |
| 27.5° | 222.3   |
| 30°   | 139.7   |
| 32.5° | 94.2    |
| 35°   | 61.0    |
| 37.5° | 34.0    |
| 40°   | 17.8    |
| 42.5° | 10.0    |
| 45°   | 6.2     |
| 47.5° | 3.9     |
| 50°   | 2.3     |
| 52.5° | 1.5     |
| 55°   | 0.8     |
| 57.5° | 0.8     |
| 60°   | 0.8     |
| 62.5° | 0.8     |
| 65°   | 0.8     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report



TEST NUMBER: P1268068  
CATALOG NUMBER: P3A20R159735D010 E3D1LI

### CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)