

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268074

Luminaire Tested: P3A20R159735D010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R159735D010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1634.0 lumens
Efficiency: N/A
Efficacy: 56.7 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268074
CATALOG NUMBER: P3A20R159735D010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1268074
 CATALOG NUMBER: P3A20R159735D010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1395875
5°	1239046
10°	860461
15°	508857
20°	289825
25°	165663
30°	91660
35°	48881
40°	27022
45°	14637
50°	9143
55°	7226
60°	6228
65°	5707
70°	5065
75°	5338
80°	3915
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14637 cd/sqm



TEST NUMBER: P1268074
 CATALOG NUMBER: P3A20R159735D010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	478.7	29.3
10°-20°	631.7	38.7
20°-30°	325.3	19.9
30°-40°	122.1	7.5
40°-50°	40.0	2.4
50°-60°	17.2	1.1
60°-70°	10.9	0.7
70°-80°	6.4	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1435.7	87.9
0°-40°	1557.8	95.3
0°-60°	1614.9	98.8
0°-90°	1634.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1634.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6366	
5°	5629	479
15°	2242	632
25°	685	325
35°	183	122
45°	47	40
55°	19	17
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1268074
CATALOG NUMBER: P3A20R159735D010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6365.7
1°	6353.1
2°	6269.6
3°	6110.7
4°	5901.3
5°	5629.0
6°	5320.5
7°	4982.0
8°	4605.8
9°	4234.3
10°	3864.4
12.5°	2973.5
15°	2241.5
17.5°	1678.0
20°	1242.0
22.5°	927.1
25°	684.7
27.5°	499.0
30°	362.0
32.5°	256.6
35°	182.6
37.5°	130.7
40°	94.4
42.5°	67.7
45°	47.2
47.5°	34.6
50°	26.8
52.5°	22.0
55°	18.9
57.5°	15.7
60°	14.2
62.5°	12.6
65°	11.0
67.5°	9.4
70°	7.9
72.5°	7.9
75°	6.3
77.5°	4.7
80°	3.1
82.5°	3.1
85°	1.6
87.5°	0.0
90°	0.0

(END OF REPORT)