

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270277

Luminaire Tested: P3A17R509740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R509740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 688.0 lumens
Efficiency: N/A
Efficacy: 32.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270277

CATALOG NUMBER: P3A17R509740DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270277

CATALOG NUMBER: P3A17R509740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219039
5°	214637
10°	201043
15°	179978
20°	151447
25°	115603
30°	75125
35°	44544
40°	25734
45°	12901
50°	4810
55°	3747
60°	3508
65°	3165
70°	3142
75°	3135
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12901 cd/sqm

TEST NUMBER: P1270277

CATALOG NUMBER: P3A17R509740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	13.2
10°-20°	219.2	31.9
20°-30°	215.1	31.3
30°-40°	108.4	15.8
40°-50°	34.2	5.0
50°-60°	8.9	1.3
60°-70°	6.3	0.9
70°-80°	3.9	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.0	76.3
0°-40°	633.4	92.1
0°-60°	676.6	98.3
0°-90°	688.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	688.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	999	
5°	975	91
15°	793	219
25°	478	215
35°	166	108
45°	42	34
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1270277

CATALOG NUMBER: P3A17R509740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	998.9
2.5°	992.8
5°	975.1
7.5°	943.3
10°	902.9
12.5°	850.9
15°	792.8
17.5°	725.5
20°	649.0
22.5°	566.4
25°	477.8
27.5°	383.5
30°	296.7
32.5°	223.3
35°	166.4
37.5°	123.0
40°	89.9
42.5°	63.6
45°	41.6
47.5°	23.9
50°	14.1
52.5°	10.4
55°	9.8
57.5°	8.6
60°	8.0
62.5°	7.3
65°	6.1
67.5°	5.5
70°	4.9
72.5°	4.3
75°	3.7
77.5°	3.1
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)