

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270345

Luminaire Tested: P3A17R609740DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270345
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R609740DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1028.0 lumens
Efficiency: N/A
Efficacy: 48.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270345
CATALOG NUMBER: P3A17R609740DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1270345

CATALOG NUMBER: P3A17R609740DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82	82	82	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67	67	67	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61	61	61	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56	56	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182485
5°	180431
10°	174190
15°	164564
20°	151680
25°	137355
30°	121943
35°	104213
40°	82870
45°	58425
50°	34899
55°	17662
60°	16972
65°	15514
70°	14426
75°	13725
80°	12628
85°	9309

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 58425 cd/sqm



TEST NUMBER: P1270345
 CATALOG NUMBER: P3A17R609740DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	7.5
10°-20°	202.6	19.7
20°-30°	260.1	25.3
30°-40°	241.2	23.5
40°-50°	146.8	14.3
50°-60°	48.9	4.8
60°-70°	29.8	2.9
70°-80°	16.8	1.6
80°-90°	4.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.8	52.5
0°-40°	780.9	76.0
0°-60°	976.7	95.0
0°-90°	1028.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1028.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	832	
5°	820	77
15°	725	203
25°	568	260
35°	389	241
45°	188	147
55°	46	49
65°	30	30
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P1270345
CATALOG NUMBER: P3A17R609740DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	832.2
2.5°	828.5
5°	819.7
7.5°	803.5
10°	782.3
12.5°	756.1
15°	724.9
17.5°	688.7
20°	650.0
22.5°	608.9
25°	567.7
27.5°	525.3
30°	481.6
32.5°	437.9
35°	389.3
37.5°	338.1
40°	289.5
42.5°	238.3
45°	188.4
47.5°	146.0
50°	102.3
52.5°	61.1
55°	46.2
57.5°	42.4
60°	38.7
62.5°	33.7
65°	29.9
67.5°	26.2
70°	22.5
72.5°	18.7
75°	16.2
77.5°	12.5
80°	10.0
82.5°	6.2
85°	3.7
87.5°	2.5
90°	0.0

(END OF REPORT)