

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268136

Luminaire Tested: P3A20R259735D010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1268136  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R259735D010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 620.0 lumens  
Efficiency: N/A  
Efficacy: 21.5 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268136  
CATALOG NUMBER: P3A20R259735D010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1268136

CATALOG NUMBER: P3A20R259735D010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70				70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	147357
5°	143825
10°	133286
15°	118707
20°	102022
25°	86715
30°	71378
35°	55626
40°	40018
45°	25398
50°	15010
55°	10322
60°	9473
65°	8821
70°	7950
75°	7202
80°	6819
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25398 cd/sqm



TEST NUMBER: P1268136  
 CATALOG NUMBER: P3A20R259735D010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.6	9.8
10°-20°	145.2	23.4
20°-30°	164.0	26.5
30°-40°	129.7	20.9
40°-50°	65.5	10.6
50°-60°	26.2	4.2
60°-70°	16.8	2.7
70°-80°	9.3	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.8	59.6
0°-40°	499.5	80.6
0°-60°	591.3	95.4
0°-90°	620.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	620.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	672	
5°	653	61
15°	523	145
25°	358	164
35°	208	130
45°	82	66
55°	27	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1268136  
CATALOG NUMBER: P3A20R259735D010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	672.0
1°	672.0
2°	669.7
3°	665.8
4°	660.4
5°	653.4
6°	644.9
7°	634.9
8°	624.1
9°	611.7
10°	598.6
11°	583.9
12°	570.0
13°	553.8
14°	538.4
15°	522.9
17.5°	479.7
20°	437.2
22.5°	397.0
25°	358.4
27.5°	320.5
30°	281.9
32.5°	245.6
35°	207.8
37.5°	173.0
40°	139.8
42.5°	108.9
45°	81.9
47.5°	61.0
50°	44.0
52.5°	33.2
55°	27.0
57.5°	24.7
60°	21.6
62.5°	19.3
65°	17.0
67.5°	14.7
70°	12.4
72.5°	10.8
75°	8.5
77.5°	7.0
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8



TEST NUMBER: P1268136  
CATALOG NUMBER: P3A20R259735D010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)