

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268189

Luminaire Tested: P3A20R359735D010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R359735D010 E3D1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2000.1 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268189
CATALOG NUMBER: P3A20R359735D010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1268189

CATALOG NUMBER: P3A20R359735D010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93	93	93	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83	83	83	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77	77	77	77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75	75	75	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73	73	73	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70	70	70	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1304128
5°	1277567
10°	1188533
15°	871378
20°	446195
25°	160824
30°	62617
35°	21924
40°	9017
45°	2450
50°	2149
55°	2409
60°	2061
65°	1660
70°	2052
75°	2711
80°	2020
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 2711 cd/sqm



TEST NUMBER: P1268189
 CATALOG NUMBER: P3A20R359735D010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	541.1	27.1
10°-20°	1015.2	50.8
20°-30°	359.4	18.0
30°-40°	62.9	3.1
40°-50°	9.2	0.5
50°-60°	5.1	0.3
60°-70°	3.7	0.2
70°-80°	2.7	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1915.7	95.8
0°-40°	1978.7	98.9
0°-60°	1993.0	99.6
0°-90°	2000.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2000.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5947	
5°	5804	541
15°	3838	1015
25°	665	359
35°	82	63
45°	8	9
55°	6	5
65°	3	4
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1268189
CATALOG NUMBER: P3A20R359735D010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5947.3
1°	5945.7
2°	5926.8
3°	5890.6
4°	5857.5
5°	5804.0
6°	5748.9
7°	5687.4
8°	5611.8
9°	5493.7
10°	5337.8
11°	5122.0
12°	4862.1
13°	4553.4
14°	4213.2
15°	3838.4
17.5°	2858.7
20°	1912.1
22.5°	1152.9
25°	664.7
27.5°	396.9
30°	247.3
32.5°	143.3
35°	81.9
37.5°	52.0
40°	31.5
42.5°	15.8
45°	7.9
47.5°	6.3
50°	6.3
52.5°	6.3
55°	6.3
57.5°	4.7
60°	4.7
62.5°	4.7
65°	3.2
67.5°	3.2
70°	3.2
72.5°	3.2
75°	3.2
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0



TEST NUMBER: P1268189
CATALOG NUMBER: P3A20R359735D010 E3D1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)