

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268193

Luminaire Tested: P3A20R359735D010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R359735D010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1655.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268193
CATALOG NUMBER: P3A20R359735D010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1268193
 CATALOG NUMBER: P3A20R359735D010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	67	67	67	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	834714
5°	802199
10°	698963
15°	535372
20°	358174
25°	216738
30°	124374
35°	69546
40°	36955
45°	19041
50°	9143
55°	7226
60°	6885
65°	5707
70°	6027
75°	5338
80°	5935
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19041 cd/sqm



TEST NUMBER: P1268193
 CATALOG NUMBER: P3A20R359735D010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	331.6	20.0
10°-20°	642.6	38.8
20°-30°	420.7	25.4
30°-40°	170.7	10.3
40°-50°	51.2	3.1
50°-60°	17.4	1.1
60°-70°	11.7	0.7
70°-80°	6.8	0.4
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1394.9	84.3
0°-40°	1565.5	94.6
0°-60°	1634.1	98.7
0°-90°	1655.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1655.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3807	
5°	3644	332
15°	2358	643
25°	896	421
35°	260	171
45°	61	51
55°	19	17
65°	11	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1268193
CATALOG NUMBER: P3A20R359735D010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3806.6
1°	3800.3
2°	3783.0
3°	3748.3
4°	3707.4
5°	3644.4
6°	3565.7
7°	3477.6
8°	3378.4
9°	3265.0
10°	3139.1
11°	2999.0
12°	2852.6
13°	2688.9
14°	2533.0
15°	2358.3
17.5°	1934.8
20°	1534.9
22.5°	1180.7
25°	895.8
27.5°	667.5
30°	491.2
32.5°	360.5
35°	259.8
37.5°	184.2
40°	129.1
42.5°	89.7
45°	61.4
47.5°	40.9
50°	26.8
52.5°	20.5
55°	18.9
57.5°	17.3
60°	15.7
62.5°	14.2
65°	11.0
67.5°	9.4
70°	9.4
72.5°	7.9
75°	6.3
77.5°	4.7
80°	4.7
82.5°	3.1
85°	1.6
87.5°	1.6



TEST NUMBER: P1268193
CATALOG NUMBER: P3A20R359735D010 E3DL1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)