

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426774

Luminaire Tested: P3A17RH9740DE010 E3HY1WMH

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17RH9740DE010 E3HY1WMH
Description: 3in Adjustable LED luminaire with, RH optic, 4000K CCT AND, 97CRI , E3HY1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 761.9 lumens
Efficiency: N/A
Efficacy: 35.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426774

CATALOG NUMBER: P3A17RH9740DE010 E3HY1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1426774

CATALOG NUMBER: P3A17RH9740DE010 E3HY1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	104	100	98	100	98	96		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87
5	96	89	84	81	95	88	84	80	87	83	79		85	82	79		84
6	93	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	69	65	73	68	65		72	68	65		71
10	79	71	66	62	78	70	66	62	70	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	380869
5°	345278
10°	299015
15°	271738
20°	151587
25°	94118
30°	75455
35°	41064
40°	20696
45°	9272
50°	2968
55°	459
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9272 cd/sqm

TEST NUMBER: P1426774

CATALOG NUMBER: P3A17RH9740DE010 E3HY1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.3	18.7
10°-20°	303.4	39.8
20°-30°	186.6	24.5
30°-40°	101.8	13.4
40°-50°	25.5	3.3
50°-60°	2.3	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	632.3	83.0
0°-40°	734.2	96.4
0°-60°	761.9	100.0
0°-90°	761.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1737	
5°	1569	142
15°	1197	303
25°	389	187
35°	153	102
45°	30	25
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426774

CATALOG NUMBER: P3A17RH9740DE010 E3HY1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1736.9
2.5°	1693.3
5°	1568.6
7.5°	1436.4
10°	1342.9
12.5°	1271.8
15°	1197.0
17.5°	952.6
20°	649.6
22.5°	435.2
25°	389.0
27.5°	347.9
30°	298.0
32.5°	223.2
35°	153.4
37.5°	104.7
40°	72.3
42.5°	48.6
45°	29.9
47.5°	16.2
50°	8.7
52.5°	3.7
55°	1.2
57.5°	1.2
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)