

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268230

Luminaire Tested: P3A20R409735D010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R409735D010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1407.0 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268230
CATALOG NUMBER: P3A20R409735D010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1268230

CATALOG NUMBER: P3A20R409735D010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315852
5°	310125
10°	292313
15°	265518
20°	233260
25°	199197
30°	165013
35°	127261
40°	90570
45°	61030
50°	33295
55°	23473
60°	22103
65°	20443
70°	18144
75°	17368
80°	13891
85°	11825

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61030 cd/sqm



TEST NUMBER: P1268230
 CATALOG NUMBER: P3A20R409735D010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.4	9.3
10°-20°	325.8	23.2
20°-30°	376.6	26.8
30°-40°	296.8	21.1
40°-50°	152.4	10.8
50°-60°	58.3	4.1
60°-70°	38.6	2.7
70°-80°	20.9	1.5
80°-90°	6.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.8	59.3
0°-40°	1130.7	80.4
0°-60°	1341.3	95.3
0°-90°	1407.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1407.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1440	
5°	1409	131
15°	1170	326
25°	823	377
35°	475	297
45°	197	152
55°	61	58
65°	39	39
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P1268230
CATALOG NUMBER: P3A20R409735D010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1440.4
2.5°	1432.5
5°	1408.9
7.5°	1367.9
10°	1312.8
12.5°	1248.3
15°	1169.6
17.5°	1087.7
20°	999.6
22.5°	909.9
25°	823.3
27.5°	736.7
30°	651.7
32.5°	565.1
35°	475.4
37.5°	392.0
40°	316.4
42.5°	251.9
45°	196.8
47.5°	143.2
50°	97.6
52.5°	70.8
55°	61.4
57.5°	55.1
60°	50.4
62.5°	44.1
65°	39.4
67.5°	33.1
70°	28.3
72.5°	23.6
75°	20.5
77.5°	15.7
80°	11.0
82.5°	9.4
85°	4.7
87.5°	3.1
90°	0.0

(END OF REPORT)