

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270447

Luminaire Tested: P3A20R159740D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R159740D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2117.0 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270447

CATALOG NUMBER: P3A20R159740D010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1270447

CATALOG NUMBER: P3A20R159740D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	105		104	103	102		101	100	99
2	112	109	107	105		110	108	105	103		105	103	101		102	100	99		99	98	97
3	110	106	102	100		108	104	102	99		102	100	98		100	98	96		98	96	95
4	107	102	99	96		106	101	98	96		99	97	95		98	96	94		96	94	93
5	105	100	96	94		103	99	96	93		97	94	92		96	93	92		94	93	91
6	102	97	94	91		101	96	93	91		95	92	90		94	92	90		93	91	89
7	100	95	91	89		99	94	91	89		93	90	88		92	90	88		91	89	88
8	98	93	89	87		97	92	89	87		91	89	87		91	88	86		90	88	86
9	96	91	88	85		96	91	87	85		90	87	85		89	87	85		89	86	85
10	95	89	86	84		94	89	86	84		88	85	83		88	85	83		87	85	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4031322
5°	3287269
10°	1609901
15°	492761
20°	208665
25°	94384
30°	36790
35°	16972
40°	5296
45°	1985
50°	819
55°	306
60°	351
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1985 cd/sqm

TEST NUMBER: P1270447

CATALOG NUMBER: P3A20R159740D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1162.4	54.9
10°-20°	713.3	33.7
20°-30°	191.6	9.1
30°-40°	42.2	2.0
40°-50°	5.9	0.3
50°-60°	1.1	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2067.3	97.7
0°-40°	2109.5	99.6
0°-60°	2116.5	100.0
0°-90°	2117.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2117.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18384	
5°	14934	###
15°	2171	713
25°	390	192
35°	63	42
45°	6	6
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270447

CATALOG NUMBER: P3A20R159740D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	18384.3
1°	18269.5
2°	17901.0
3°	17237.2
4°	16237.7
5°	14934.1
6°	13459.5
7°	11817.1
8°	10307.9
9°	8708.1
10°	7230.2
11°	5767.7
12°	4437.5
13°	3413.2
14°	2702.0
15°	2170.6
17.5°	1345.4
20°	894.2
22.5°	602.1
25°	390.1
27.5°	231.2
30°	145.3
32.5°	97.9
35°	63.4
37.5°	35.3
40°	18.5
42.5°	10.4
45°	6.4
47.5°	4.0
50°	2.4
52.5°	1.6
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1270447
CATALOG NUMBER: P3A20R159740D010 E3D1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)