

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270449

Luminaire Tested: P3A20R159740D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R159740D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2117.0 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270449

CATALOG NUMBER: P3A20R159740D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1270449

CATALOG NUMBER: P3A20R159740D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	98		
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	96		
3	110	106	102	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94		
4	107	102	99	96	106	101	98	96	99	97	95	98	96	94	96	94	93	92		
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	93	91	90		
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	88		
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87		
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	85		
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	89	86	85	84		
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	82		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4031322
5°	3287269
10°	1609901
15°	492761
20°	208665
25°	94384
30°	36790
35°	16972
40°	5296
45°	1985
50°	819
55°	306
60°	351
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1985 cd/sqm

TEST NUMBER: P1270449

CATALOG NUMBER: P3A20R159740D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1162.4	54.9
10°-20°	713.3	33.7
20°-30°	191.6	9.1
30°-40°	42.2	2.0
40°-50°	5.9	0.3
50°-60°	1.1	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2067.3	97.7
0°-40°	2109.5	99.6
0°-60°	2116.5	100.0
0°-90°	2117.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2117.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18384	
5°	14934	###
15°	2171	713
25°	390	192
35°	63	42
45°	6	6
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270449

CATALOG NUMBER: P3A20R159740D010 E3D1WH

CANDELA DISTRIBUTION (FULL):


	0°
0°	18384.3
1°	18269.5
2°	17901.0
3°	17237.2
4°	16237.7
5°	14934.1
6°	13459.5
7°	11817.1
8°	10307.9
9°	8708.1
10°	7230.2
11°	5767.7
12°	4437.5
13°	3413.2
14°	2702.0
15°	2170.6
17.5°	1345.4
20°	894.2
22.5°	602.1
25°	390.1
27.5°	231.2
30°	145.3
32.5°	97.9
35°	63.4
37.5°	35.3
40°	18.5
42.5°	10.4
45°	6.4
47.5°	4.0
50°	2.4
52.5°	1.6
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1270449

CATALOG NUMBER: P3A20R159740D010 E3D1WH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)