

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266103

Luminaire Tested: P3A02R109735DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R109735DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 164.0 lumens
Efficiency: N/A
Efficacy: 43.2 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266103

CATALOG NUMBER: P3A02R109735DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266103

CATALOG NUMBER: P3A02R109735DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	83	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	70	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47715
5°	44750
10°	36695
15°	28491
20°	22495
25°	17928
30°	14382
35°	11752
40°	9675
45°	8156
50°	6993
55°	6040
60°	5350
65°	4670
70°	4167
75°	3389
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8156 cd/sqm

TEST NUMBER: P1266103

CATALOG NUMBER: P3A02R109735DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	11.1
10°-20°	35.2	21.4
20°-30°	34.2	20.8
30°-40°	27.6	16.8
40°-50°	20.5	12.5
50°-60°	14.3	8.7
60°-70°	9.0	5.5
70°-80°	4.3	2.6
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	87.5	53.3
0°-40°	115.1	70.2
0°-60°	150.0	91.4
0°-90°	164.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	164.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	218	
5°	203	18
15°	126	35
25°	74	34
35°	44	28
45°	26	21
55°	16	14
65°	9	9
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1266103

CATALOG NUMBER: P3A02R109735DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	217.6
2.5°	214.0
5°	203.3
7.5°	186.0
10°	164.8
12.5°	143.9
15°	125.5
17.5°	110.1
20°	96.4
22.5°	84.5
25°	74.1
27.5°	64.8
30°	56.8
32.5°	50.0
35°	43.9
37.5°	38.5
40°	33.8
42.5°	29.9
45°	26.3
47.5°	23.4
50°	20.5
52.5°	18.0
55°	15.8
57.5°	14.0
60°	12.2
62.5°	10.4
65°	9.0
67.5°	7.6
70°	6.5
72.5°	5.0
75°	4.0
77.5°	2.9
80°	2.2
82.5°	1.1
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)