

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270724

Luminaire Tested: P3A20R609740D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R609740D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1350.0 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270724
CATALOG NUMBER: P3A20R609740D010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1270724
 CATALOG NUMBER: P3A20R609740D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91				91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82				82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61				61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47				47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44				44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239652
5°	236957
10°	228742
15°	216119
20°	199191
25°	180373
30°	160151
35°	136844
40°	108804
45°	76721
50°	45849
55°	23168
60°	22279
65°	20391
70°	18913
75°	18046
80°	16543
85°	12328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 76721 cd/sqm



TEST NUMBER: P1270724
 CATALOG NUMBER: P3A20R609740D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.2	7.5
10°-20°	266.0	19.7
20°-30°	341.6	25.3
30°-40°	316.7	23.5
40°-50°	192.8	14.3
50°-60°	64.3	4.8
60°-70°	39.1	2.9
70°-80°	22.0	1.6
80°-90°	6.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	708.8	52.5
0°-40°	1025.5	76.0
0°-60°	1282.6	95.0
0°-90°	1350.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1350.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1093	
5°	1076	101
15°	952	266
25°	746	342
35°	511	317
45°	247	193
55°	61	64
65°	39	39
75°	21	22
85°	5	6
90°	0	



TEST NUMBER: P1270724
CATALOG NUMBER: P3A20R609740D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1092.9
2.5°	1088.0
5°	1076.5
7.5°	1055.2
10°	1027.3
12.5°	992.9
15°	952.0
17.5°	904.4
20°	853.6
22.5°	799.6
25°	745.5
27.5°	689.8
30°	632.5
32.5°	575.1
35°	511.2
37.5°	444.0
40°	380.1
42.5°	313.0
45°	247.4
47.5°	191.7
50°	134.4
52.5°	80.3
55°	60.6
57.5°	55.7
60°	50.8
62.5°	44.2
65°	39.3
67.5°	34.4
70°	29.5
72.5°	24.6
75°	21.3
77.5°	16.4
80°	13.1
82.5°	8.2
85°	4.9
87.5°	3.3
90°	0.0

(END OF REPORT)