

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266242

Luminaire Tested: P3A02R309735DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266242
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R309735DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 240.0 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266242
CATALOG NUMBER: P3A02R309735DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1266242

CATALOG NUMBER: P3A02R309735DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	86	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140055
5°	133304
10°	112111
15°	80863
20°	50148
25°	28526
30°	15851
35°	8620
40°	4551
45°	2450
50°	1330
55°	879
60°	789
65°	830
70°	705
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2450 cd/sqm



TEST NUMBER: P1266242
 CATALOG NUMBER: P3A02R309735DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	22.7
10°-20°	96.9	40.4
20°-30°	56.0	23.3
30°-40°	21.3	8.9
40°-50°	6.5	2.7
50°-60°	2.2	0.9
60°-70°	1.5	0.6
70°-80°	0.8	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	207.5	86.4
0°-40°	228.7	95.3
0°-60°	237.4	98.9
0°-90°	240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	240.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	639	
5°	606	55
15°	356	97
25°	118	56
35°	32	21
45°	8	7
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266242
CATALOG NUMBER: P3A02R309735DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	638.7
1°	638.2
2°	634.4
3°	627.1
4°	618.0
5°	605.6
6°	589.7
7°	572.0
8°	552.3
9°	528.7
10°	503.5
11°	476.3
12°	447.5
13°	417.4
14°	386.8
15°	356.2
17.5°	280.9
20°	214.9
22.5°	159.4
25°	117.9
27.5°	85.7
30°	62.6
32.5°	45.1
35°	32.2
37.5°	22.4
40°	15.9
42.5°	11.1
45°	7.9
47.5°	5.4
50°	3.9
52.5°	2.7
55°	2.3
57.5°	2.0
60°	1.8
62.5°	1.6
65°	1.6
67.5°	1.4
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0



TEST NUMBER: P1266242
CATALOG NUMBER: P3A02R309735DE010 E3DL1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)