

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266250

Luminaire Tested: P3A02R309735DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1266250  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R309735DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 185.0 lumens  
Efficiency: N/A  
Efficacy: 51.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266250

CATALOG NUMBER: P3A02R309735DE010 E3DLD1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1266250

CATALOG NUMBER: P3A02R309735DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 89  |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 84  |
| 4   | 94  | 86  | 79  | 74  | 92  | 84  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 68  | 76  | 71  | 67  |  | 75  | 70  | 66  |  | 73  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 62  |  | 70  | 65  | 61  |  | 69  |
| 7   | 79  | 69  | 62  | 58  | 78  | 68  | 62  | 58  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 58  | 54  | 74  | 64  | 58  | 53  | 63  | 57  | 53  |  | 62  | 57  | 53  |  | 61  |
| 9   | 71  | 61  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 54  | 50  |  | 58  | 53  | 50  |  | 57  |
| 10  | 68  | 57  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 50  | 47  |  | 55  | 50  | 46  |  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 43703 |
| 5°  | 42725 |
| 10° | 39723 |
| 15° | 35346 |
| 20° | 30406 |
| 25° | 25768 |
| 30° | 21370 |
| 35° | 16784 |
| 40° | 12023 |
| 45° | 7877  |
| 50° | 4503  |
| 55° | 2944  |
| 60° | 2807  |
| 65° | 2594  |
| 70° | 2308  |
| 75° | 2118  |
| 80° | 2020  |
| 85° | 1761  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7877 cd/sqm

TEST NUMBER: P1266250

CATALOG NUMBER: P3A02R309735DE010 E3DLD1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 18.0   | 9.7       |
| 10°-20°   | 43.3   | 23.4      |
| 20°-30°   | 48.8   | 26.4      |
| 30°-40°   | 39.0   | 21.1      |
| 40°-50°   | 20.0   | 10.8      |
| 50°-60°   | 7.5    | 4.1       |
| 60°-70°   | 4.9    | 2.7       |
| 70°-80°   | 2.7    | 1.4       |
| 80°-90°   | 0.8    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 110.1  | 59.5      |
| 0°-40°    | 149.1  | 80.6      |
| 0°-60°    | 176.6  | 95.5      |
| 0°-90°    | 185.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 185.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 199 |      |
| 5°  | 194 | 18   |
| 15° | 156 | 43   |
| 25° | 106 | 49   |
| 35° | 63  | 39   |
| 45° | 25  | 20   |
| 55° | 8   | 8    |
| 65° | 5   | 5    |
| 75° | 2   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1266250

CATALOG NUMBER: P3A02R309735DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 199.3 |
| 1°    | 199.3 |
| 2°    | 198.6 |
| 3°    | 197.5 |
| 4°    | 195.9 |
| 5°    | 194.1 |
| 6°    | 191.8 |
| 7°    | 188.9 |
| 8°    | 185.7 |
| 9°    | 182.1 |
| 10°   | 178.4 |
| 11°   | 174.3 |
| 12°   | 170.0 |
| 13°   | 165.5 |
| 14°   | 160.7 |
| 15°   | 155.7 |
| 17.5° | 143.0 |
| 20°   | 130.3 |
| 22.5° | 118.0 |
| 25°   | 106.5 |
| 27.5° | 95.1  |
| 30°   | 84.4  |
| 32.5° | 73.6  |
| 35°   | 62.7  |
| 37.5° | 52.0  |
| 40°   | 42.0  |
| 42.5° | 33.1  |
| 45°   | 25.4  |
| 47.5° | 18.8  |
| 50°   | 13.2  |
| 52.5° | 9.3   |
| 55°   | 7.7   |
| 57.5° | 7.0   |
| 60°   | 6.4   |
| 62.5° | 5.7   |
| 65°   | 5.0   |
| 67.5° | 4.3   |
| 70°   | 3.6   |
| 72.5° | 3.0   |
| 75°   | 2.5   |
| 77.5° | 2.0   |
| 80°   | 1.6   |
| 82.5° | 1.1   |
| 85°   | 0.7   |
| 87.5° | 0.2   |



TEST NUMBER: P1266250

CATALOG NUMBER: P3A02R309735DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)