

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268568

Luminaire Tested: P3A02R209740DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R209740DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 186.0 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268568
CATALOG NUMBER: P3A02R209740DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1268568
 CATALOG NUMBER: P3A02R209740DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.8	10.1
10°-20°	44.5	23.9
20°-30°	49.4	26.5
30°-40°	37.7	20.2
40°-50°	19.3	10.4
50°-60°	7.9	4.3
60°-70°	5.0	2.7
70°-80°	2.8	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	112.6	60.6
0°-40°	150.3	80.8
0°-60°	177.5	95.4
0°-90°	186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	210	
5°	203	19
15°	160	44
25°	108	49
35°	60	38
45°	24	19
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1268568
CATALOG NUMBER: P3A02R209740DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	209.8
1°	210.0
2°	209.1
3°	207.9
4°	206.0
5°	203.4
6°	200.4
7°	197.1
8°	193.5
9°	189.3
10°	185.0
12.5°	172.7
15°	159.7
17.5°	146.5
20°	133.3
22.5°	120.0
25°	108.0
27.5°	95.9
30°	83.4
32.5°	71.6
35°	60.0
37.5°	49.9
40°	39.9
42.5°	31.4
45°	24.3
47.5°	18.4
50°	13.7
52.5°	10.2
55°	8.0
57.5°	7.3
60°	6.4
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.8
72.5°	3.1
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)