

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266311

Luminaire Tested: P3A02R409735DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R409735DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 82.0 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266311

CATALOG NUMBER: P3A02R409735DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1266311

CATALOG NUMBER: P3A02R409735DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25524
5°	25005
10°	23291
15°	20295
20°	16358
25°	12267
30°	8609
35°	5648
40°	3406
45°	2047
50°	1228
55°	994
60°	877
65°	778
70°	705
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2047 cd/sqm

TEST NUMBER: P1266311

CATALOG NUMBER: P3A02R409735DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.6	12.9
10°-20°	24.6	30.0
20°-30°	23.2	28.3
30°-40°	13.4	16.4
40°-50°	5.3	6.5
50°-60°	2.4	2.9
60°-70°	1.5	1.8
70°-80°	0.8	0.9
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	58.4	71.2
0°-40°	71.8	87.6
0°-60°	79.5	97.0
0°-90°	82.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	82.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	116	
5°	114	11
15°	89	25
25°	51	23
35°	21	13
45°	7	5
55°	3	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1266311

CATALOG NUMBER: P3A02R409735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	116.4
2.5°	115.8
5°	113.6
7.5°	109.7
10°	104.6
12.5°	97.7
15°	89.4
17.5°	80.2
20°	70.1
22.5°	60.1
25°	50.7
27.5°	42.0
30°	34.0
32.5°	27.1
35°	21.1
37.5°	16.0
40°	11.9
42.5°	8.9
45°	6.6
47.5°	4.8
50°	3.6
52.5°	2.9
55°	2.6
57.5°	2.3
60°	2.0
62.5°	1.7
65°	1.5
67.5°	1.2
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.6
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)