

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268630

Luminaire Tested: P3A02R309740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268630
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R309740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 75.0 lumens
Efficiency: N/A
Efficacy: 20.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268630
CATALOG NUMBER: P3A02R309740DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1268630
 CATALOG NUMBER: P3A02R309740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 95 | 93 | 93 | 93 | 93 |
| 2 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 97 | 94 | 92 | 94 | 92 | 90 | 92 | 90 | 88 | 86 | 86 | 86 | 86 |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 86 | 91 | 87 | 84 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | 80 | 80 | 80 |
| 4 | 97 | 89 | 84 | 79 | 95 | 88 | 83 | 79 | 86 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 74 | 74 | 74 | 74 |
| 5 | 92 | 84 | 78 | 73 | 90 | 83 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 72 | 78 | 74 | 71 | 70 | 70 | 70 | 70 |
| 6 | 88 | 79 | 73 | 68 | 86 | 78 | 72 | 68 | 76 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 65 | 65 | 65 | 65 |
| 7 | 83 | 74 | 68 | 64 | 82 | 74 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 63 | 70 | 66 | 63 | 61 | 61 | 61 | 61 |
| 8 | 80 | 70 | 64 | 60 | 78 | 70 | 64 | 60 | 69 | 63 | 60 | 68 | 63 | 60 | 67 | 62 | 59 | 58 | 58 | 58 | 58 |
| 9 | 76 | 67 | 61 | 57 | 75 | 66 | 61 | 57 | 65 | 60 | 56 | 64 | 60 | 56 | 63 | 59 | 56 | 55 | 55 | 55 | 55 |
| 10 | 73 | 63 | 58 | 54 | 72 | 63 | 57 | 54 | 62 | 57 | 54 | 61 | 57 | 53 | 61 | 56 | 53 | 52 | 52 | 52 | 52 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 25634 |
| 5° | 24829 |
| 10° | 22378 |
| 15° | 18502 |
| 20° | 14328 |
| 25° | 10743 |
| 30° | 7799 |
| 35° | 5193 |
| 40° | 3206 |
| 45° | 1861 |
| 50° | 1160 |
| 55° | 918 |
| 60° | 833 |
| 65° | 675 |
| 70° | 577 |
| 75° | 593 |
| 80° | 379 |
| 85° | 503 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1861 cd/sqm



TEST NUMBER: P1268630
 CATALOG NUMBER: P3A02R309740DE010 E3DLP1GPH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 10.4 | 13.8 |
| 10°-20° | 22.5 | 30.0 |
| 20°-30° | 20.4 | 27.2 |
| 30°-40° | 12.4 | 16.5 |
| 40°-50° | 4.9 | 6.6 |
| 50°-60° | 2.2 | 2.9 |
| 60°-70° | 1.3 | 1.8 |
| 70°-80° | 0.7 | 1.0 |
| 80°-90° | 0.2 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 53.2 | 71.0 |
| 0°-40° | 65.6 | 87.5 |
| 0°-60° | 72.7 | 97.0 |
| 0°-90° | 75.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 75.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 117 | |
| 5° | 113 | 10 |
| 15° | 82 | 22 |
| 25° | 44 | 20 |
| 35° | 19 | 12 |
| 45° | 6 | 5 |
| 55° | 2 | 2 |
| 65° | 1 | 1 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1268630
CATALOG NUMBER: P3A02R309740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 116.9 |
| 1° | 116.8 |
| 2° | 116.3 |
| 3° | 115.5 |
| 4° | 114.3 |
| 5° | 112.8 |
| 6° | 110.9 |
| 7° | 109.0 |
| 8° | 106.4 |
| 9° | 103.5 |
| 10° | 100.5 |
| 11° | 97.0 |
| 12° | 93.3 |
| 13° | 89.5 |
| 14° | 85.5 |
| 15° | 81.5 |
| 17.5° | 71.2 |
| 20° | 61.4 |
| 22.5° | 52.3 |
| 25° | 44.4 |
| 27.5° | 37.2 |
| 30° | 30.8 |
| 32.5° | 24.9 |
| 35° | 19.4 |
| 37.5° | 14.9 |
| 40° | 11.2 |
| 42.5° | 8.1 |
| 45° | 6.0 |
| 47.5° | 4.5 |
| 50° | 3.4 |
| 52.5° | 2.7 |
| 55° | 2.4 |
| 57.5° | 2.1 |
| 60° | 1.9 |
| 62.5° | 1.5 |
| 65° | 1.3 |
| 67.5° | 1.2 |
| 70° | 0.9 |
| 72.5° | 0.8 |
| 75° | 0.7 |
| 77.5° | 0.6 |
| 80° | 0.3 |
| 82.5° | 0.2 |
| 85° | 0.2 |
| 87.5° | 0.1 |



TEST NUMBER: P1268630
CATALOG NUMBER: P3A02R309740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)