

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266512

Luminaire Tested: P3A05R109735DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1266512  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R109735DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 251.0 lumens  
Efficiency: N/A  
Efficacy: 31.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266512  
CATALOG NUMBER: P3A05R109735DE010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1266512  
 CATALOG NUMBER: P3A05R109735DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	108237
5°	100044
10°	79869
15°	60341
20°	45947
25°	35010
30°	25067
35°	16356
40°	10047
45°	6078
50°	4025
55°	3135
60°	2675
65°	2335
70°	2116
75°	2033
80°	1515
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6078 cd/sqm



TEST NUMBER: P1266512  
 CATALOG NUMBER: P3A05R109735DE010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.3	16.0
10°-20°	74.3	29.6
20°-30°	66.1	26.3
30°-40°	39.1	15.6
40°-50°	16.1	6.4
50°-60°	7.5	3.0
60°-70°	4.6	1.8
70°-80°	2.4	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	180.7	72.0
0°-40°	219.8	87.6
0°-60°	243.4	97.0
0°-90°	251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	251.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	494	
5°	454	40
15°	266	74
25°	145	66
35°	61	39
45°	20	16
55°	8	8
65°	4	5
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1266512  
CATALOG NUMBER: P3A05R109735DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	493.6
1°	492.4
2°	488.7
3°	481.4
4°	469.1
5°	454.5
6°	438.6
7°	419.8
8°	400.3
9°	380.3
10°	358.7
12.5°	309.4
15°	265.8
17.5°	228.3
20°	196.9
22.5°	169.2
25°	144.7
27.5°	121.1
30°	99.0
32.5°	79.1
35°	61.1
37.5°	46.9
40°	35.1
42.5°	26.1
45°	19.6
47.5°	15.1
50°	11.8
52.5°	9.8
55°	8.2
57.5°	6.9
60°	6.1
62.5°	5.3
65°	4.5
67.5°	4.1
70°	3.3
72.5°	2.9
75°	2.4
77.5°	1.6
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)