

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268678

Luminaire Tested: P3A02R409740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R409740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 135.0 lumens
Efficiency: N/A
Efficacy: 37.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268678

CATALOG NUMBER: P3A02R409740DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268678

CATALOG NUMBER: P3A02R409740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84		
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80		
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76		
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72		
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65		
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63		
10	78	70	65	62	78	70	65	62	69	64	61	68	64	61	67	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59732
5°	58001
10°	52638
15°	43474
20°	31363
25°	19404
30°	10508
35°	5434
40°	2948
45°	1644
50°	819
55°	612
60°	570
65°	519
70°	513
75°	508
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1644 cd/sqm

TEST NUMBER: P1268678

CATALOG NUMBER: P3A02R409740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.3	18.0
10°-20°	52.1	38.6
20°-30°	37.2	27.6
30°-40°	13.7	10.2
40°-50°	4.3	3.2
50°-60°	1.5	1.1
60°-70°	1.0	0.8
70°-80°	0.6	0.5
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	113.7	84.2
0°-40°	127.4	94.4
0°-60°	133.2	98.7
0°-90°	135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	135.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	272	
5°	264	24
15°	192	52
25°	80	37
35°	20	14
45°	5	4
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268678

CATALOG NUMBER: P3A02R409740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	272.4
2.5°	270.3
5°	263.5
7.5°	252.1
10°	236.4
12.5°	216.3
15°	191.5
17.5°	163.7
20°	134.4
22.5°	105.6
25°	80.2
27.5°	58.9
30°	41.5
32.5°	29.1
35°	20.3
37.5°	14.4
40°	10.3
42.5°	7.4
45°	5.3
47.5°	3.6
50°	2.4
52.5°	1.7
55°	1.6
57.5°	1.5
60°	1.3
62.5°	1.2
65°	1.0
67.5°	0.9
70°	0.8
72.5°	0.7
75°	0.6
77.5°	0.5
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)