

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266656

Luminaire Tested: P3A05R309735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266656
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R309735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 186.0 lumens
Efficiency: N/A
Efficacy: 25.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266656

CATALOG NUMBER: P3A05R309735DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266656

CATALOG NUMBER: P3A05R309735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43944
5°	42945
10°	39946
15°	35551
20°	30569
25°	25889
30°	21497
35°	16865
40°	12080
45°	7939
50°	4503
55°	2982
60°	2807
65°	2594
70°	2372
75°	2118
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7939 cd/sqm

TEST NUMBER: P1266656

CATALOG NUMBER: P3A05R309735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.1	9.7
10°-20°	43.5	23.4
20°-30°	49.0	26.4
30°-40°	39.2	21.1
40°-50°	20.1	10.8
50°-60°	7.6	4.1
60°-70°	5.0	2.7
70°-80°	2.7	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	110.7	59.5
0°-40°	149.9	80.6
0°-60°	177.6	95.5
0°-90°	186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	200	
5°	195	18
15°	157	44
25°	107	49
35°	63	39
45°	26	20
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1266656

CATALOG NUMBER: P3A05R309735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	200.4
1°	200.4
2°	199.7
3°	198.6
4°	197.0
5°	195.1
6°	192.9
7°	189.9
8°	186.7
9°	183.0
10°	179.4
11°	175.3
12°	171.0
13°	166.4
14°	161.6
15°	156.6
17.5°	143.8
20°	131.0
22.5°	118.7
25°	107.0
27.5°	95.6
30°	84.9
32.5°	73.9
35°	63.0
37.5°	52.3
40°	42.2
42.5°	33.3
45°	25.6
47.5°	18.9
50°	13.2
52.5°	9.4
55°	7.8
57.5°	7.1
60°	6.4
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.7
72.5°	3.0
75°	2.5
77.5°	2.1
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.2



TEST NUMBER: P1266656

CATALOG NUMBER: P3A05R309735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)