

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268756

Luminaire Tested: P3A02R559740DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R559740DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 305.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268756
CATALOG NUMBER: P3A02R559740DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1268756
 CATALOG NUMBER: P3A02R559740DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88436
5°	85318
10°	88375
15°	87129
20°	80624
25°	65205
30°	39069
35°	13251
40°	3635
45°	1613
50°	478
55°	76
60°	44
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1613 cd/sqm



TEST NUMBER: P1268756
 CATALOG NUMBER: P3A02R559740DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	12.3
10°-20°	106.8	35.0
20°-30°	118.8	38.9
30°-40°	37.0	12.1
40°-50°	4.4	1.5
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	263.1	86.3
0°-40°	300.1	98.4
0°-60°	304.8	100.0
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	403	
5°	388	38
15°	384	107
25°	270	119
35°	50	37
45°	5	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1268756
CATALOG NUMBER: P3A02R559740DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	403.3
1°	401.8
2°	397.9
3°	393.0
4°	388.6
5°	387.6
6°	388.7
7°	391.2
8°	394.0
9°	396.2
10°	396.9
11°	396.4
12°	394.5
13°	391.6
14°	388.3
15°	383.8
16°	378.6
17°	371.9
18°	364.5
19°	355.6
20°	345.5
21°	334.1
22°	320.5
23°	305.6
24°	288.4
25°	269.5
26°	248.8
27°	226.8
28°	203.2
29°	179.0
30°	154.3
31°	129.5
32°	105.3
32.5°	94.6
33°	83.4
34°	64.5
35°	49.5
36°	37.7
37°	27.9
37.5°	23.9
38°	20.7
39°	15.8
40°	12.7
42.5°	8.1
45°	5.2



TEST NUMBER: P1268756
CATALOG NUMBER: P3A02R559740DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	3.1
50°	1.4
52.5°	0.5
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)