

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268845

Luminaire Tested: P3A02R709740DE010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1268845  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R709740DE010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 295.0 lumens  
Efficiency: N/A  
Efficacy: 81.9 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268845  
CATALOG NUMBER: P3A02R709740DE010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1268845  
 CATALOG NUMBER: P3A02R709740DE010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58570
5°	55888
10°	53172
15°	51760
20°	49844
25°	47180
30°	43880
35°	36861
40°	23759
45°	11040
50°	2900
55°	726
60°	746
65°	623
70°	577
75°	593
80°	631
85°	503

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11040 cd/sqm



TEST NUMBER: P1268845  
 CATALOG NUMBER: P3A02R709740DE010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.8	8.1
10°-20°	64.1	21.7
20°-30°	89.5	30.3
30°-40°	83.0	28.1
40°-50°	29.8	10.1
50°-60°	2.5	0.9
60°-70°	1.3	0.4
70°-80°	0.8	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.3	60.1
0°-40°	260.3	88.3
0°-60°	292.6	99.2
0°-90°	295.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	295.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	267	
5°	254	24
15°	228	64
25°	195	90
35°	138	83
45°	36	30
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1268845  
CATALOG NUMBER: P3A02R709740DE010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	267.1
2.5°	263.1
5°	253.9
7.5°	245.4
10°	238.8
12.5°	233.4
15°	228.0
17.5°	221.4
20°	213.6
22.5°	204.7
25°	195.0
27.5°	185.1
30°	173.3
32.5°	158.2
35°	137.7
37.5°	111.5
40°	83.0
42.5°	56.6
45°	35.6
47.5°	19.8
50°	8.5
52.5°	2.8
55°	1.9
57.5°	1.7
60°	1.7
62.5°	1.4
65°	1.2
67.5°	1.2
70°	0.9
72.5°	0.9
75°	0.7
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)