

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266788

Luminaire Tested: P3A05R559735DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1266788  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R559735DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 97CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 602.0 lumens  
Efficiency: N/A  
Efficacy: 83.6 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266788

CATALOG NUMBER: P3A05R559735DE010 E3D1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1266788

CATALOG NUMBER: P3A05R559735DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 111 | 109 | 107 |  | 112 | 109 | 107 | 105 |  | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  | 97  | 96  |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 92  | 91  |
| 3   | 104 | 98  | 94  | 90  |  | 102 | 97  | 93  | 90  |  | 95  | 91  | 88  |  | 92  | 89  | 87  |  | 90  | 88  | 86  |
| 4   | 100 | 93  | 88  | 84  |  | 98  | 92  | 87  | 84  |  | 90  | 86  | 83  |  | 88  | 84  | 82  |  | 86  | 83  | 81  |
| 5   | 95  | 88  | 83  | 79  |  | 94  | 87  | 82  | 78  |  | 85  | 81  | 78  |  | 84  | 80  | 77  |  | 82  | 79  | 76  |
| 6   | 91  | 83  | 78  | 74  |  | 90  | 82  | 77  | 74  |  | 81  | 76  | 73  |  | 80  | 76  | 73  |  | 78  | 75  | 72  |
| 7   | 87  | 79  | 73  | 70  |  | 86  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 76  | 72  | 69  |  | 75  | 71  | 68  |
| 8   | 83  | 75  | 69  | 66  |  | 82  | 74  | 69  | 66  |  | 73  | 69  | 65  |  | 72  | 68  | 65  |  | 71  | 68  | 65  |
| 9   | 80  | 71  | 66  | 62  |  | 79  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 62  |  | 68  | 64  | 61  |
| 10  | 77  | 68  | 62  | 59  |  | 76  | 67  | 62  | 59  |  | 67  | 62  | 59  |  | 66  | 62  | 59  |  | 65  | 61  | 58  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 174569 |
| 5°  | 168390 |
| 10° | 174412 |
| 15° | 171965 |
| 20° | 159147 |
| 25° | 128717 |
| 30° | 77126  |
| 35° | 26154  |
| 40° | 7214   |
| 45° | 3194   |
| 50° | 921    |
| 55° | 191    |
| 60° | 88     |
| 65° | 104    |
| 70° | 128    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 3194 cd/sqm

TEST NUMBER: P1266788

CATALOG NUMBER: P3A05R559735DE010 E3D1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 74.0   | 12.3      |
| 10°-20°   | 210.9  | 35.0      |
| 20°-30°   | 234.4  | 38.9      |
| 30°-40°   | 73.0   | 12.1      |
| 40°-50°   | 8.8    | 1.5       |
| 50°-60°   | 0.7    | 0.1       |
| 60°-70°   | 0.2    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 519.3  | 86.3      |
| 0°-40°    | 592.3  | 98.4      |
| 0°-60°    | 601.7  | 100.0     |
| 0°-90°    | 602.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 602.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 796 |      |
| 5°  | 765 | 74   |
| 15° | 758 | 211  |
| 25° | 532 | 234  |
| 35° | 98  | 73   |
| 45° | 10  | 9    |
| 55° | 0   | 1    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1266788

CATALOG NUMBER: P3A05R559735DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 796.1 |
| 1°    | 793.1 |
| 2°    | 785.4 |
| 3°    | 775.8 |
| 4°    | 767.1 |
| 5°    | 765.0 |
| 6°    | 767.3 |
| 7°    | 772.1 |
| 8°    | 777.6 |
| 9°    | 781.9 |
| 10°   | 783.3 |
| 11°   | 782.4 |
| 12°   | 778.7 |
| 13°   | 773.0 |
| 14°   | 766.4 |
| 15°   | 757.5 |
| 16°   | 747.2 |
| 17°   | 734.1 |
| 18°   | 719.5 |
| 19°   | 701.9 |
| 20°   | 682.0 |
| 21°   | 659.4 |
| 22°   | 632.6 |
| 23°   | 603.1 |
| 24°   | 569.2 |
| 25°   | 532.0 |
| 26°   | 491.0 |
| 27°   | 447.6 |
| 28°   | 401.1 |
| 29°   | 353.3 |
| 30°   | 304.6 |
| 31°   | 255.7 |
| 32°   | 207.9 |
| 32.5° | 186.6 |
| 33°   | 164.7 |
| 34°   | 127.4 |
| 35°   | 97.7  |
| 36°   | 74.3  |
| 37°   | 55.1  |
| 37.5° | 47.1  |
| 38°   | 40.9  |
| 39°   | 31.1  |
| 40°   | 25.2  |
| 42.5° | 16.0  |
| 45°   | 10.3  |

TEST NUMBER: P1266788

CATALOG NUMBER: P3A05R559735DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 47.5° | 6.2 |
| 50°   | 2.7 |
| 52.5° | 0.9 |
| 55°   | 0.5 |
| 57.5° | 0.2 |
| 60°   | 0.2 |
| 62.5° | 0.2 |
| 65°   | 0.2 |
| 67.5° | 0.2 |
| 70°   | 0.2 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)