

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266940

Luminaire Tested: P3A09R159735DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1266940  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R159735DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 708.0 lumens  
Efficiency: N/A  
Efficacy: 63.8 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266940  
CATALOG NUMBER: P3A09R159735DE010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1266940

CATALOG NUMBER: P3A09R159735DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	604820
5°	536869
10°	372828
15°	220478
20°	125568
25°	71786
30°	39728
35°	21174
40°	11708
45°	6357
50°	3957
55°	3135
60°	2675
65°	2491
70°	2180
75°	2288
80°	1768
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6357 cd/sqm



TEST NUMBER: P1266940

CATALOG NUMBER: P3A09R159735DE010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	207.4	29.3
10°-20°	273.7	38.7
20°-30°	140.9	19.9
30°-40°	52.9	7.5
40°-50°	17.3	2.4
50°-60°	7.4	1.0
60°-70°	4.7	0.7
70°-80°	2.8	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.1	87.9
0°-40°	675.0	95.3
0°-60°	699.7	98.8
0°-90°	708.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2758	
5°	2439	207
15°	971	274
25°	297	141
35°	79	53
45°	20	17
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1266940  
CATALOG NUMBER: P3A09R159735DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2758.2
1°	2752.7
2°	2716.6
3°	2647.7
4°	2557.0
5°	2439.0
6°	2305.3
7°	2158.7
8°	1995.7
9°	1834.7
10°	1674.4
12.5°	1288.4
15°	971.2
17.5°	727.1
20°	538.1
22.5°	401.7
25°	296.7
27.5°	216.2
30°	156.9
32.5°	111.2
35°	79.1
37.5°	56.6
40°	40.9
42.5°	29.3
45°	20.5
47.5°	15.0
50°	11.6
52.5°	9.5
55°	8.2
57.5°	6.8
60°	6.1
62.5°	5.5
65°	4.8
67.5°	4.1
70°	3.4
72.5°	3.4
75°	2.7
77.5°	2.0
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)