

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269009

Luminaire Tested: P3A05R259740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R259740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 152.0 lumens
Efficiency: N/A
Efficacy: 21.1 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269009
CATALOG NUMBER: P3A05R259740DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1269009

CATALOG NUMBER: P3A05R259740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55193
5°	52938
10°	46381
15°	37276
20°	28632
25°	21679
30°	15648
35°	10413
40°	6298
45°	3659
50°	2354
55°	1912
60°	1667
65°	1453
70°	1218
75°	1186
80°	884
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3659 cd/sqm



TEST NUMBER: P1269009
 CATALOG NUMBER: P3A05R259740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.9	14.4
10°-20°	45.4	29.9
20°-30°	41.1	27.0
30°-40°	24.7	16.2
40°-50°	9.8	6.4
50°-60°	4.5	3.0
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.4	71.3
0°-40°	133.0	87.5
0°-60°	147.4	96.9
0°-90°	152.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	152.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	252	
5°	240	22
15°	164	45
25°	90	41
35°	39	25
45°	12	10
55°	5	5
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1269009
CATALOG NUMBER: P3A05R259740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	251.7
1°	251.7
2°	250.5
3°	247.9
4°	244.6
5°	240.5
6°	235.3
7°	229.4
8°	222.5
9°	215.6
10°	208.3
11°	199.8
12°	191.0
13°	182.2
14°	173.5
15°	164.2
17.5°	142.4
20°	122.7
22.5°	105.0
25°	89.6
27.5°	75.1
30°	61.8
32.5°	49.8
35°	38.9
37.5°	29.6
40°	22.0
42.5°	16.1
45°	11.8
47.5°	9.0
50°	6.9
52.5°	5.7
55°	5.0
57.5°	4.3
60°	3.8
62.5°	3.1
65°	2.8
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.4
77.5°	1.2
80°	0.7
82.5°	0.5
85°	0.5
87.5°	0.2



TEST NUMBER: P1269009
CATALOG NUMBER: P3A05R259740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)