

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266995

Luminaire Tested: P3A09R259735DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R259735DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 922.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266995
CATALOG NUMBER: P3A09R259735DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1266995
 CATALOG NUMBER: P3A09R259735DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	90	88	86	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	88	86	84	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	86	84	82	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	83	80	78	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1009766
5°	935393
10°	723723
15°	345677
20°	113970
25°	48051
30°	18610
35°	8058
40°	2691
45°	1240
50°	443
55°	268
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1240 cd/sqm



TEST NUMBER: P1266995
 CATALOG NUMBER: P3A09R259735DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.5	40.5
10°-20°	424.8	46.1
20°-30°	98.7	10.7
30°-40°	20.7	2.2
40°-50°	3.3	0.4
50°-60°	0.6	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	897.1	97.3
0°-40°	917.8	99.6
0°-60°	921.7	100.0
0°-90°	922.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	922.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4605	
5°	4250	374
15°	1523	425
25°	199	99
35°	30	21
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1266995
CATALOG NUMBER: P3A09R259735DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4604.9
1°	4595.5
2°	4547.7
3°	4480.5
4°	4377.9
5°	4249.5
6°	4084.7
7°	3912.2
8°	3718.7
9°	3500.4
10°	3250.3
11°	2960.5
12°	2627.9
13°	2263.5
14°	1882.4
15°	1522.7
16°	1204.5
17°	938.4
18°	738.1
19°	590.4
20°	488.4
21°	408.2
22°	342.7
23°	286.2
24°	239.4
25°	198.6
27.5°	117.7
30°	73.5
32.5°	47.1
35°	30.1
37.5°	18.1
40°	9.4
42.5°	6.0
45°	4.0
47.5°	2.3
50°	1.3
52.5°	0.7
55°	0.7
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0



TEST NUMBER: P1266995
CATALOG NUMBER: P3A09R259735DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)