

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267045

Luminaire Tested: P3A09R309735DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R309735DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 440.0 lumens
Efficiency: N/A
Efficacy: 39.6 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267045
CATALOG NUMBER: P3A09R309735DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1267045
 CATALOG NUMBER: P3A09R309735DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150361
5°	145674
10°	131260
15°	108582
20°	84054
25°	63052
30°	45779
35°	30490
40°	18749
45°	11009
50°	6755
55°	5467
60°	4780
65°	3891
70°	3526
75°	3474
80°	2526
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11009 cd/sqm



TEST NUMBER: P1267045
 CATALOG NUMBER: P3A09R309735DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.9	13.8
10°-20°	131.7	29.9
20°-30°	119.8	27.2
30°-40°	72.4	16.5
40°-50°	29.1	6.6
50°-60°	12.9	2.9
60°-70°	7.8	1.8
70°-80°	4.2	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	312.4	71.0
0°-40°	384.9	87.5
0°-60°	426.8	97.0
0°-90°	440.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	440.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	686	
5°	662	61
15°	478	132
25°	261	120
35°	114	72
45°	36	29
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1267045
CATALOG NUMBER: P3A09R309735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	685.7
1°	685.0
2°	682.3
3°	677.5
4°	670.7
5°	661.8
6°	650.9
7°	639.3
8°	624.3
9°	607.2
10°	589.5
11°	569.0
12°	547.2
13°	525.3
14°	501.5
15°	478.3
17.5°	417.5
20°	360.2
22.5°	307.0
25°	260.6
27.5°	218.3
30°	180.8
32.5°	146.0
35°	113.9
37.5°	87.3
40°	65.5
42.5°	47.8
45°	35.5
47.5°	26.6
50°	19.8
52.5°	15.7
55°	14.3
57.5°	12.3
60°	10.9
62.5°	8.9
65°	7.5
67.5°	6.8
70°	5.5
72.5°	4.8
75°	4.1
77.5°	3.4
80°	2.0
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1267045
CATALOG NUMBER: P3A09R309735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)