

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267201

Luminaire Tested: P3A09R609735DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R609735DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 717.0 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267201

CATALOG NUMBER: P3A09R609735DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1267201

CATALOG NUMBER: P3A09R609735DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169307
5°	167708
10°	162812
15°	152532
20°	135018
25°	112942
30°	88520
35°	64219
40°	42709
45°	26638
50°	14430
55°	4167
60°	3903
65°	3528
70°	3526
75°	3474
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26638 cd/sqm

TEST NUMBER: P1267201

CATALOG NUMBER: P3A09R609735DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.7	10.0
10°-20°	186.4	26.0
20°-30°	212.5	29.6
30°-40°	150.7	21.0
40°-50°	68.4	9.5
50°-60°	14.5	2.0
60°-70°	7.0	1.0
70°-80°	4.3	0.6
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.6	65.6
0°-40°	621.3	86.7
0°-60°	704.2	98.2
0°-90°	717.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	772	
5°	762	72
15°	672	186
25°	467	212
35°	240	151
45°	86	68
55°	11	15
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1267201

CATALOG NUMBER: P3A09R609735DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	772.1
2.5°	769.4
5°	761.9
7.5°	748.9
10°	731.2
12.5°	706.0
15°	671.9
17.5°	629.0
20°	578.6
22.5°	524.0
25°	466.8
27.5°	408.2
30°	349.6
32.5°	293.7
35°	239.9
37.5°	192.2
40°	149.2
42.5°	113.1
45°	85.9
47.5°	64.1
50°	42.3
52.5°	19.8
55°	10.9
57.5°	9.5
60°	8.9
62.5°	8.2
65°	6.8
67.5°	6.1
70°	5.5
72.5°	4.8
75°	4.1
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)