

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267213

Luminaire Tested: P3A09R609735DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267213  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R609735DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 496.0 lumens  
Efficiency: N/A  
Efficacy: 44.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267213  
CATALOG NUMBER: P3A09R609735DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1267213  
 CATALOG NUMBER: P3A09R609735DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	125692
5°	122892
10°	115050
15°	103202
20°	88744
25°	73383
30°	57984
35°	43072
40°	29656
45°	18607
50°	10234
55°	6002
60°	5394
65°	4618
70°	3911
75°	4067
80°	3410
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18607 cd/sqm



TEST NUMBER: P1267213  
 CATALOG NUMBER: P3A09R609735DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.0	10.5
10°-20°	126.3	25.5
20°-30°	138.5	27.9
30°-40°	100.9	20.3
40°-50°	47.7	9.6
50°-60°	15.6	3.1
60°-70°	8.8	1.8
70°-80°	4.8	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.7	63.9
0°-40°	417.6	84.2
0°-60°	480.9	97.0
0°-90°	496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	496.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	573	
5°	558	52
15°	455	126
25°	303	138
35°	161	101
45°	60	48
55°	16	16
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1267213  
CATALOG NUMBER: P3A09R609735DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	573.2
2.5°	569.8
5°	558.3
7.5°	540.5
10°	516.7
12.5°	488.0
15°	454.6
17.5°	418.5
20°	380.3
22.5°	341.5
25°	303.3
27.5°	265.2
30°	229.0
32.5°	194.3
35°	160.9
37.5°	130.9
40°	103.6
42.5°	79.8
45°	60.0
47.5°	43.6
50°	30.0
52.5°	19.8
55°	15.7
57.5°	13.6
60°	12.3
62.5°	10.2
65°	8.9
67.5°	7.5
70°	6.1
72.5°	5.5
75°	4.8
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)