

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269066

Luminaire Tested: P3A05R359740DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1269066  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R359740DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 392.0 lumens  
Efficiency: N/A  
Efficacy: 54.4 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1269066  
CATALOG NUMBER: P3A05R359740DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1269066

CATALOG NUMBER: P3A05R359740DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	89554
5°	87651
10°	82074
15°	73689
20°	64102
25°	54608
30°	45754
35°	36433
40°	26335
45°	16684
50°	9074
55°	6308
60°	5964
65°	5552
70°	5257
75°	4490
80°	4293
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16684 cd/sqm



TEST NUMBER: P1269066  
 CATALOG NUMBER: P3A05R359740DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.1	9.5
10°-20°	90.3	23.0
20°-30°	103.5	26.4
30°-40°	84.4	21.5
40°-50°	42.6	10.9
50°-60°	15.8	4.0
60°-70°	10.6	2.7
70°-80°	5.9	1.5
80°-90°	1.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.9	58.9
0°-40°	315.3	80.4
0°-60°	373.8	95.3
0°-90°	392.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	392.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	408	
5°	398	37
15°	325	90
25°	226	104
35°	136	84
45°	54	43
55°	16	16
65°	11	11
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1269066

CATALOG NUMBER: P3A05R359740DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	408.4
1°	407.9
2°	406.9
3°	405.0
4°	402.1
5°	398.2
6°	393.3
7°	388.5
8°	382.2
9°	375.9
10°	368.6
11°	360.9
12°	352.6
13°	343.4
14°	333.8
15°	324.6
17.5°	299.8
20°	274.7
22.5°	249.0
25°	225.7
27.5°	203.0
30°	180.7
32.5°	158.4
35°	136.1
37.5°	113.8
40°	92.0
42.5°	71.7
45°	53.8
47.5°	38.8
50°	26.6
52.5°	19.4
55°	16.5
57.5°	15.0
60°	13.6
62.5°	12.1
65°	10.7
67.5°	9.2
70°	8.2
72.5°	6.8
75°	5.3
77.5°	4.4
80°	3.4
82.5°	2.4
85°	1.5
87.5°	1.0



TEST NUMBER: P1269066  
CATALOG NUMBER: P3A05R359740DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)