

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269069

Luminaire Tested: P3A05R359740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R359740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 154.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269069
CATALOG NUMBER: P3A05R359740DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1269069

CATALOG NUMBER: P3A05R359740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49492
5°	48272
10°	44132
15°	37458
20°	29659
25°	22429
30°	16332
35°	11056
40°	6784
45°	3907
50°	2354
55°	1912
60°	1667
65°	1453
70°	1218
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3907 cd/sqm



TEST NUMBER: P1269069

CATALOG NUMBER: P3A05R359740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.3	13.2
10°-20°	45.5	29.5
20°-30°	42.6	27.6
30°-40°	26.1	16.9
40°-50°	10.3	6.7
50°-60°	4.5	2.9
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.3	70.3
0°-40°	134.4	87.3
0°-60°	149.2	96.9
0°-90°	154.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	154.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	226	
5°	219	20
15°	165	45
25°	93	43
35°	41	26
45°	13	10
55°	5	5
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P1269069

CATALOG NUMBER: P3A05R359740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	225.7
1°	226.0
2°	225.3
3°	223.8
4°	221.7
5°	219.3
6°	216.3
7°	212.7
8°	208.4
9°	203.7
10°	198.2
11°	192.5
12°	186.4
13°	179.7
14°	172.4
15°	165.0
17.5°	146.1
20°	127.1
22.5°	108.8
25°	92.7
27.5°	77.8
30°	64.5
32.5°	52.2
35°	41.3
37.5°	31.5
40°	23.7
42.5°	17.1
45°	12.6
47.5°	9.0
50°	6.9
52.5°	5.7
55°	5.0
57.5°	4.3
60°	3.8
62.5°	3.3
65°	2.8
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.4
77.5°	1.2
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2



TEST NUMBER: P1269069
CATALOG NUMBER: P3A05R359740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)