

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267255

Luminaire Tested: P3A09R709735DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R709735DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 853.0 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267255
CATALOG NUMBER: P3A09R709735DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1267255
 CATALOG NUMBER: P3A09R709735DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169372
5°	161633
10°	153771
15°	149672
20°	144143
25°	136411
30°	126880
35°	106595
40°	68700
45°	31910
50°	8358
55°	2103
60°	2105
65°	1764
70°	1731
75°	1694
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31910 cd/sqm



TEST NUMBER: P1267255
 CATALOG NUMBER: P3A09R709735DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.7	8.1
10°-20°	185.3	21.7
20°-30°	258.8	30.3
30°-40°	240.0	28.1
40°-50°	86.0	10.1
50°-60°	7.3	0.9
60°-70°	3.6	0.4
70°-80°	2.3	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	512.8	60.1
0°-40°	752.8	88.3
0°-60°	846.1	99.2
0°-90°	853.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	853.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	772	
5°	734	69
15°	659	185
25°	564	259
35°	398	240
45°	103	86
55°	6	7
65°	3	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1267255
CATALOG NUMBER: P3A09R709735DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	772.4
2.5°	760.9
5°	734.3
7.5°	709.7
10°	690.6
12.5°	675.0
15°	659.3
17.5°	640.2
20°	617.7
22.5°	591.8
25°	563.8
27.5°	535.2
30°	501.1
32.5°	457.5
35°	398.2
37.5°	322.5
40°	240.0
42.5°	163.6
45°	102.9
47.5°	57.3
50°	24.5
52.5°	8.2
55°	5.5
57.5°	4.8
60°	4.8
62.5°	4.1
65°	3.4
67.5°	3.4
70°	2.7
72.5°	2.7
75°	2.0
77.5°	2.0
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)