

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269100

Luminaire Tested: P3A05R409740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R409740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 433.0 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269100

CATALOG NUMBER: P3A05R409740DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269100

CATALOG NUMBER: P3A05R409740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97207
5°	95443
10°	89956
15°	81703
20°	71780
25°	61310
30°	50793
35°	39163
40°	27881
45°	18793
50°	10234
55°	7226
60°	6798
65°	6278
70°	5578
75°	5338
80°	4293
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18793 cd/sqm

TEST NUMBER: P1269100

CATALOG NUMBER: P3A05R409740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	9.3
10°-20°	100.3	23.2
20°-30°	115.9	26.8
30°-40°	91.3	21.1
40°-50°	46.9	10.8
50°-60°	17.9	4.1
60°-70°	11.9	2.7
70°-80°	6.4	1.5
80°-90°	1.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.6	59.3
0°-40°	348.0	80.4
0°-60°	412.8	95.3
0°-90°	433.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	433.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	443	
5°	434	40
15°	360	100
25°	253	116
35°	146	91
45°	61	47
55°	19	18
65°	12	12
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1269100

CATALOG NUMBER: P3A05R409740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	443.3
2.5°	440.8
5°	433.6
7.5°	421.0
10°	404.0
12.5°	384.2
15°	359.9
17.5°	334.7
20°	307.6
22.5°	280.0
25°	253.4
27.5°	226.7
30°	200.6
32.5°	173.9
35°	146.3
37.5°	120.6
40°	97.4
42.5°	77.5
45°	60.6
47.5°	44.1
50°	30.0
52.5°	21.8
55°	18.9
57.5°	17.0
60°	15.5
62.5°	13.6
65°	12.1
67.5°	10.2
70°	8.7
72.5°	7.3
75°	6.3
77.5°	4.8
80°	3.4
82.5°	2.9
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)