

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269725

Luminaire Tested: P3A13R159740DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R159740DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1190.9 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269725

CATALOG NUMBER: P3A13R159740DE010 E3D1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1269725

CATALOG NUMBER: P3A13R159740DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105		111	108	106	104		105	103	101		102	101	99		99	98	97
3	110	106	103	100		108	105	102	100		102	100	98		100	98	97		98	97	95
4	107	103	100	97		106	102	99	97		100	97	95		98	96	94		97	95	93
5	105	100	97	94		104	99	96	94		98	95	93		96	94	92		95	93	92
6	103	98	94	92		102	97	94	92		96	93	91		95	92	91		94	92	90
7	101	96	92	90		100	95	92	90		94	91	89		93	91	89		92	90	89
8	99	94	90	88		98	93	90	88		92	90	88		92	89	87		91	89	87
9	97	92	89	87		97	92	89	87		91	88	86		90	88	86		90	87	86
10	96	90	87	85		95	90	87	85		89	87	85		89	86	85		88	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2315012
5°	1940211
10°	913922
15°	275529
20°	101952
25°	39631
30°	14787
35°	4524
40°	1603
45°	868
50°	648
55°	726
60°	833
65°	467
70°	577
75°	763
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 868 cd/sqm

TEST NUMBER: P1269725

CATALOG NUMBER: P3A13R159740DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	681.4	57.2
10°-20°	405.1	34.0
20°-30°	85.1	7.1
30°-40°	13.7	1.2
40°-50°	2.3	0.2
50°-60°	1.7	0.1
60°-70°	1.0	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1171.6	98.4
0°-40°	1185.3	99.5
0°-60°	1189.3	99.9
0°-90°	1190.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1190.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10557	
5°	8814	681
15°	1214	405
25°	164	85
35°	17	14
45°	3	2
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1269725

CATALOG NUMBER: P3A13R159740DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	10557.3
1°	10524.4
2°	10356.8
3°	10021.6
4°	9530.0
5°	8814.4
6°	7973.6
7°	7012.2
8°	6094.1
9°	5054.6
10°	4104.5
12.5°	2214.7
15°	1213.7
17.5°	710.9
20°	436.9
22.5°	267.4
25°	163.8
27.5°	98.9
30°	58.4
32.5°	33.0
35°	16.9
37.5°	9.4
40°	5.6
42.5°	3.8
45°	2.8
47.5°	1.9
50°	1.9
52.5°	1.9
55°	1.9
57.5°	1.9
60°	1.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)