

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269847

Luminaire Tested: P3A13R359740DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1269847  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R359740DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 989.0 lumens  
Efficiency: N/A  
Efficacy: 67.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1269847

CATALOG NUMBER: P3A13R359740DE010 E3DL1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1269847

CATALOG NUMBER: P3A13R359740DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 87  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  |  | 81  | 77  | 75  |  | 80  |
| 7   | 89  | 81  | 76  | 72  | 88  | 80  | 75  | 72  | 79  | 75  | 71  |  | 78  | 74  | 71  |  | 77  |
| 8   | 85  | 77  | 72  | 69  | 84  | 77  | 72  | 69  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  |
| 9   | 82  | 74  | 69  | 66  | 81  | 74  | 69  | 65  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  |
| 10  | 79  | 71  | 66  | 63  | 78  | 71  | 66  | 63  | 70  | 66  | 63  |  | 69  | 65  | 62  |  | 69  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 498798 |
| 5°  | 479396 |
| 10° | 417694 |
| 15° | 319934 |
| 20° | 214032 |
| 25° | 129516 |
| 30° | 74315  |
| 35° | 41546  |
| 40° | 22070  |
| 45° | 11381  |
| 50° | 5458   |
| 55° | 4320   |
| 60° | 4122   |
| 65° | 3424   |
| 70° | 3590   |
| 75° | 3219   |
| 80° | 3536   |
| 85° | 2264   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11381 cd/sqm

TEST NUMBER: P1269847

CATALOG NUMBER: P3A13R359740DE010 E3DL1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 198.2  | 20.0      |
| 10°-20°   | 384.0  | 38.8      |
| 20°-30°   | 251.4  | 25.4      |
| 30°-40°   | 102.0  | 10.3      |
| 40°-50°   | 30.6   | 3.1       |
| 50°-60°   | 10.4   | 1.0       |
| 60°-70°   | 7.0    | 0.7       |
| 70°-80°   | 4.1    | 0.4       |
| 80°-90°   | 1.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 833.6  | 84.3      |
| 0°-40°    | 935.5  | 94.6      |
| 0°-60°    | 976.5  | 98.7      |
| 0°-90°    | 989.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 989.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2275 |      |
| 5°  | 2178 | 198  |
| 15° | 1409 | 384  |
| 25° | 535  | 251  |
| 35° | 155  | 102  |
| 45° | 37   | 31   |
| 55° | 11   | 10   |
| 65° | 7    | 7    |
| 75° | 4    | 4    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1269847

CATALOG NUMBER: P3A13R359740DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2274.7 |
| 1°    | 2271.0 |
| 2°    | 2260.6 |
| 3°    | 2239.9 |
| 4°    | 2215.5 |
| 5°    | 2177.9 |
| 6°    | 2130.8 |
| 7°    | 2078.1 |
| 8°    | 2018.9 |
| 9°    | 1951.1 |
| 10°   | 1875.9 |
| 11°   | 1792.1 |
| 12°   | 1704.7 |
| 13°   | 1606.8 |
| 14°   | 1513.7 |
| 15°   | 1409.3 |
| 17.5° | 1156.2 |
| 20°   | 917.2  |
| 22.5° | 705.6  |
| 25°   | 535.3  |
| 27.5° | 398.9  |
| 30°   | 293.5  |
| 32.5° | 215.4  |
| 35°   | 155.2  |
| 37.5° | 110.1  |
| 40°   | 77.1   |
| 42.5° | 53.6   |
| 45°   | 36.7   |
| 47.5° | 24.5   |
| 50°   | 16.0   |
| 52.5° | 12.2   |
| 55°   | 11.3   |
| 57.5° | 10.3   |
| 60°   | 9.4    |
| 62.5° | 8.5    |
| 65°   | 6.6    |
| 67.5° | 5.6    |
| 70°   | 5.6    |
| 72.5° | 4.7    |
| 75°   | 3.8    |
| 77.5° | 2.8    |
| 80°   | 2.8    |
| 82.5° | 1.9    |
| 85°   | 0.9    |
| 87.5° | 0.9    |



TEST NUMBER: P1269847

CATALOG NUMBER: P3A13R359740DE010 E3DL1H

CANDELA DISTRIBUTION (continued):



(END OF REPORT)