

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269462

Luminaire Tested: P3A09R409740DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R409740DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 993.0 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269462

CATALOG NUMBER: P3A09R409740DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1269462

CATALOG NUMBER: P3A09R409740DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88		
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85		
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82		
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79		
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76		
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73		
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70		
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	75	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	506166
5°	502508
10°	489347
15°	437119
20°	289849
25°	108587
30°	29042
35°	11350
40°	4093
45°	1954
50°	580
55°	268
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1954 cd/sqm

TEST NUMBER: P1269462

CATALOG NUMBER: P3A09R409740DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.4	21.7
10°-20°	510.2	51.4
20°-30°	231.4	23.3
30°-40°	30.0	3.0
40°-50°	5.2	0.5
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	957.0	96.4
0°-40°	987.0	99.4
0°-60°	992.8	100.0
0°-90°	993.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	993.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2308	
5°	2283	215
15°	1926	510
25°	449	231
35°	42	30
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1269462

CATALOG NUMBER: P3A09R409740DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2308.3
1°	2306.9
2°	2303.4
3°	2298.2
4°	2291.6
5°	2282.9
6°	2272.8
7°	2260.3
8°	2245.0
9°	2224.1
10°	2197.7
11°	2166.8
12°	2125.4
13°	2074.3
14°	2007.6
15°	1925.5
16°	1820.9
17°	1701.6
18°	1558.4
19°	1407.2
20°	1242.1
21°	1077.0
22°	914.3
23°	752.3
24°	593.1
25°	448.8
26°	332.3
27°	243.3
28°	182.9
29°	142.2
30°	114.7
31°	94.9
32°	79.3
32.5°	72.3
33°	65.4
34°	53.2
35°	42.4
36°	33.4
37°	26.4
37.5°	23.6
38°	20.9
39°	17.4
40°	14.3
42.5°	9.4
45°	6.3

TEST NUMBER: P1269462

CATALOG NUMBER: P3A09R409740DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	3.8
50°	1.7
52.5°	0.7
55°	0.7
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)