

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269533

Luminaire Tested: P3A09R509740DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1269533  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R509740DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 256.9 lumens  
Efficiency: N/A  
Efficacy: 23.1 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1269533  
CATALOG NUMBER: P3A09R509740DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1269533  
 CATALOG NUMBER: P3A09R509740DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	74753
5°	72727
10°	67066
15°	58979
20°	49354
25°	39123
30°	28713
35°	19729
40°	12538
45°	7008
50°	3787
55°	3173
60°	2763
65°	2542
70°	2244
75°	2033
80°	1768
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7008 cd/sqm



TEST NUMBER: P1269533  
 CATALOG NUMBER: P3A09R509740DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.6	11.9
10°-20°	72.0	28.0
20°-30°	73.6	28.6
30°-40°	46.7	18.2
40°-50°	18.6	7.2
50°-60°	7.5	2.9
60°-70°	4.8	1.9
70°-80°	2.5	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	176.2	68.6
0°-40°	222.8	86.7
0°-60°	248.9	96.9
0°-90°	256.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	341	
5°	330	31
15°	260	72
25°	162	74
35°	74	47
45°	23	19
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1269533  
CATALOG NUMBER: P3A09R509740DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	340.9
2.5°	338.4
5°	330.4
7.5°	317.9
10°	301.2
12.5°	281.4
15°	259.8
17.5°	236.2
20°	211.5
22.5°	186.8
25°	161.7
27.5°	136.7
30°	113.4
32.5°	92.5
35°	73.7
37.5°	57.7
40°	43.8
42.5°	32.3
45°	22.6
47.5°	15.3
50°	11.1
52.5°	9.4
55°	8.3
57.5°	7.3
60°	6.3
62.5°	5.6
65°	4.9
67.5°	4.2
70°	3.5
72.5°	2.8
75°	2.4
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)