

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269575

Luminaire Tested: P3A09R609740DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R609740DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 848.9 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269575
CATALOG NUMBER: P3A09R609740DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1269575
 CATALOG NUMBER: P3A09R609740DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222460
5°	209993
10°	204539
15°	199865
20°	185843
25°	166122
30°	126880
35°	73267
40°	28425
45°	11846
50°	2593
55°	382
60°	307
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11846 cd/sqm



TEST NUMBER: P1269575
 CATALOG NUMBER: P3A09R609740DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	10.6
10°-20°	245.2	28.9
20°-30°	307.2	36.2
30°-40°	171.7	20.2
40°-50°	32.6	3.8
50°-60°	1.7	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	642.5	75.7
0°-40°	814.2	95.9
0°-60°	848.5	99.9
0°-90°	848.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	848.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1014	
5°	954	90
15°	880	245
25°	687	307
35°	274	172
45°	38	33
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1269575
CATALOG NUMBER: P3A09R609740DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1014.5
1°	1010.3
2°	997.1
3°	981.5
4°	966.9
5°	954.0
6°	944.3
7°	936.0
8°	929.7
9°	923.8
10°	918.6
11°	913.4
12°	907.5
13°	900.2
14°	891.5
15°	880.4
16°	866.9
17°	851.6
18°	834.2
19°	814.4
20°	796.4
21°	776.9
22°	756.8
23°	735.6
24°	712.3
25°	686.6
26°	656.4
27°	622.7
28°	584.8
29°	544.6
30°	501.1
31°	457.4
32°	412.2
32.5°	387.6
33°	365.4
34°	319.2
35°	273.7
36°	232.7
37°	189.3
37.5°	169.5
38°	150.0
39°	120.9
40°	99.3
42.5°	60.4
45°	38.2



TEST NUMBER: P1269575
CATALOG NUMBER: P3A09R609740DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	21.2
50°	7.6
52.5°	1.7
55°	1.0
57.5°	0.7
60°	0.7
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)