

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269959

Luminaire Tested: P3A13R559740DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R559740DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1215.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269959
CATALOG NUMBER: P3A13R559740DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1269959
 CATALOG NUMBER: P3A13R559740DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79	79
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	83	75	69	66	82	74	69	65	73	69	65	72	68	65	71	68	65	63	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	352340
5°	339863
10°	352009
15°	347062
20°	321211
25°	259757
30°	155670
35°	52762
40°	14542
45°	6450
50°	1876
55°	344
60°	219
65°	259
70°	321
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6450 cd/sqm



TEST NUMBER: P1269959
 CATALOG NUMBER: P3A13R559740DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.4	12.3
10°-20°	425.6	35.0
20°-30°	473.1	38.9
30°-40°	147.3	12.1
40°-50°	17.7	1.5
50°-60°	1.4	0.1
60°-70°	0.5	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1048.2	86.3
0°-40°	1195.4	98.4
0°-60°	1214.5	100.0
0°-90°	1215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1215.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1607	
5°	1544	149
15°	1529	426
25°	1074	473
35°	197	147
45°	21	18
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1269959
CATALOG NUMBER: P3A13R559740DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1606.8
1°	1600.8
2°	1585.1
3°	1565.7
4°	1548.2
5°	1544.0
6°	1548.6
7°	1558.3
8°	1569.4
9°	1578.2
10°	1580.9
11°	1579.1
12°	1571.7
13°	1560.2
14°	1546.8
15°	1528.8
16°	1508.0
17°	1481.7
18°	1452.2
19°	1416.6
20°	1376.5
21°	1330.8
22°	1276.7
23°	1217.2
24°	1148.9
25°	1073.6
26°	991.0
27°	903.3
28°	809.6
29°	713.2
30°	614.8
31°	516.1
32°	419.6
32.5°	376.7
33°	332.3
34°	257.1
35°	197.1
36°	150.0
37°	111.2
37.5°	95.1
38°	82.6
39°	62.8
40°	50.8
42.5°	32.3
45°	20.8



TEST NUMBER: P1269959
CATALOG NUMBER: P3A13R559740DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	12.5
50°	5.5
52.5°	1.8
55°	0.9
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)