

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269980

Luminaire Tested: P3A13R609740DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R609740DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1217.0 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269980

CATALOG NUMBER: P3A13R609740DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1269980

CATALOG NUMBER: P3A13R609740DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	70	68
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63
8	80	70	64	60		78	70	64	60		69	64	60		68	63	60		67	63	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290613
5°	279088
10°	287347
15°	291035
20°	256992
25°	216569
30°	175647
35°	114385
40°	52527
45°	20126
50°	6755
55°	1797
60°	1667
65°	1453
70°	1218
75°	1610
80°	1137
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20126 cd/sqm

TEST NUMBER: P1269980

CATALOG NUMBER: P3A13R609740DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.0	10.0
10°-20°	351.1	28.8
20°-30°	409.5	33.6
30°-40°	264.2	21.7
40°-50°	59.2	4.9
50°-60°	5.9	0.5
60°-70°	2.8	0.2
70°-80°	1.6	0.1
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.6	72.5
0°-40°	1146.8	94.2
0°-60°	1212.0	99.6
0°-90°	1217.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1217.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1325	
5°	1268	122
15°	1282	351
25°	895	409
35°	427	264
45°	65	59
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1269980

CATALOG NUMBER: P3A13R609740DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1325.3
2.5°	1303.7
5°	1267.9
7.5°	1266.0
10°	1290.5
12.5°	1306.5
15°	1282.0
17.5°	1208.6
20°	1101.3
22.5°	989.3
25°	895.1
27.5°	802.9
30°	693.7
32.5°	565.7
35°	427.3
37.5°	291.8
40°	183.5
42.5°	110.1
45°	64.9
47.5°	37.7
50°	19.8
52.5°	6.6
55°	4.7
57.5°	3.8
60°	3.8
62.5°	2.8
65°	2.8
67.5°	2.8
70°	1.9
72.5°	1.9
75°	1.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)