

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270023

Luminaire Tested: P3A13R659740DE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1270023  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R659740DE010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 651.9 lumens  
Efficiency: N/A  
Efficacy: 44.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270023  
CATALOG NUMBER: P3A13R659740DE010 E3DL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1270023  
 CATALOG NUMBER: P3A13R659740DE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	165732
5°	161611
10°	150498
15°	134870
20°	116490
25°	96877
30°	76392
35°	56617
40°	39016
45°	24189
50°	13134
55°	8258
60°	7017
65°	6330
70°	5450
75°	4745
80°	4799
85°	4780

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24189 cd/sqm



TEST NUMBER: P1270023  
 CATALOG NUMBER: P3A13R659740DE010 E3DL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.2	10.5
10°-20°	165.1	25.3
20°-30°	182.6	28.0
30°-40°	132.6	20.3
40°-50°	62.1	9.5
50°-60°	20.9	3.2
60°-70°	12.1	1.9
70°-80°	6.3	1.0
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.9	63.8
0°-40°	548.5	84.1
0°-60°	631.5	96.9
0°-90°	651.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	651.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	756	
5°	734	68
15°	594	165
25°	400	183
35°	212	133
45°	78	62
55°	22	21
65°	12	12
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1270023  
CATALOG NUMBER: P3A13R659740DE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	755.8
2.5°	751.1
5°	734.2
7.5°	708.8
10°	675.9
12.5°	637.3
15°	594.1
17.5°	547.1
20°	499.2
22.5°	449.3
25°	400.4
27.5°	350.6
30°	301.7
32.5°	254.7
35°	211.5
37.5°	172.0
40°	136.3
42.5°	104.3
45°	78.0
47.5°	56.4
50°	38.5
52.5°	26.3
55°	21.6
57.5°	18.8
60°	16.0
62.5°	14.1
65°	12.2
67.5°	10.3
70°	8.5
72.5°	7.5
75°	5.6
77.5°	4.7
80°	3.8
82.5°	2.8
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)