

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270050

Luminaire Tested: P3A13R709740DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1270050  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R709740DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 947.9 lumens  
Efficiency: N/A  
Efficacy: 64.9 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270050  
CATALOG NUMBER: P3A13R709740DE010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1270050

CATALOG NUMBER: P3A13R709740DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	183516
5°	181333
10°	176082
15°	168628
20°	157957
25°	143500
30°	123943
35°	98778
40°	71963
45°	47292
50°	22174
55°	6843
60°	6622
65°	6330
70°	6027
75°	6354
80°	5935
85°	4780

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 47292 cd/sqm



TEST NUMBER: P1270050

CATALOG NUMBER: P3A13R709740DE010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.6	8.2
10°-20°	207.9	21.9
20°-30°	270.2	28.5
30°-40°	229.3	24.2
40°-50°	118.2	12.5
50°-60°	22.8	2.4
60°-70°	12.3	1.3
70°-80°	7.6	0.8
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.6	58.6
0°-40°	784.9	82.8
0°-60°	925.9	97.7
0°-90°	947.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	837	
5°	824	78
15°	743	208
25°	593	270
35°	369	229
45°	152	118
55°	18	23
65°	12	12
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1270050

CATALOG NUMBER: P3A13R709740DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	836.9
2.5°	834.1
5°	823.8
7.5°	808.7
10°	790.8
12.5°	768.2
15°	742.8
17.5°	711.7
20°	676.9
22.5°	637.4
25°	593.1
27.5°	543.2
30°	489.5
32.5°	430.2
35°	369.0
37.5°	308.8
40°	251.4
42.5°	197.7
45°	152.5
47.5°	112.0
50°	65.0
52.5°	28.2
55°	17.9
57.5°	16.9
60°	15.1
62.5°	14.1
65°	12.2
67.5°	11.3
70°	9.4
72.5°	8.5
75°	7.5
77.5°	5.6
80°	4.7
82.5°	2.8
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)