

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426935

Luminaire Tested: P3A20RH9827D010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20RH9827D010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 2700K CCT AND, 98CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 683.0 lumens
Efficiency: N/A
Efficacy: 24.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426935

CATALOG NUMBER: P3A20RH9827D010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426935

CATALOG NUMBER: P3A20RH9827D010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	329360
5°	301760
10°	263678
15°	231307
20°	117050
25°	58261
30°	52692
35°	40047
40°	28138
45°	19010
50°	12145
55°	8181
60°	5614
65°	4462
70°	2757
75°	2457
80°	1768
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19010 cd/sqm

TEST NUMBER: P1426935

CATALOG NUMBER: P3A20RH9827D010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	18.3
10°-20°	258.2	37.8
20°-30°	125.9	18.4
30°-40°	94.1	13.8
40°-50°	48.4	7.1
50°-60°	20.0	2.9
60°-70°	8.1	1.2
70°-80°	3.0	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.9	74.5
0°-40°	602.9	88.3
0°-60°	671.3	98.3
0°-90°	683.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	683.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1502	
5°	1371	125
15°	1019	258
25°	241	126
35°	150	94
45°	61	48
55°	21	20
65°	9	8
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1426935

CATALOG NUMBER: P3A20RH9827D010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1502.0
2.5°	1467.8
5°	1370.9
7.5°	1266.9
10°	1184.2
12.5°	1122.9
15°	1018.9
17.5°	795.2
20°	501.6
22.5°	297.8
25°	240.8
27.5°	222.3
30°	208.1
32.5°	182.4
35°	149.6
37.5°	122.6
40°	98.3
42.5°	78.4
45°	61.3
47.5°	47.0
50°	35.6
52.5°	27.1
55°	21.4
57.5°	17.1
60°	12.8
62.5°	10.0
65°	8.6
67.5°	5.7
70°	4.3
72.5°	4.3
75°	2.9
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)