

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270158

Luminaire Tested: P3A17R309740DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R309740DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1575.0 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270158

CATALOG NUMBER: P3A17R309740DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1270158

CATALOG NUMBER: P3A17R309740DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	87	86
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1253123
5°	1236779
10°	1079829
15°	686338
20°	271927
25°	90828
30°	42260
35°	19140
40°	7357
45°	3597
50°	1058
55°	459
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3597 cd/sqm

TEST NUMBER: P1270158

CATALOG NUMBER: P3A17R309740DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	513.7	32.6
10°-20°	796.6	50.6
20°-30°	205.4	13.0
30°-40°	48.2	3.1
40°-50°	9.4	0.6
50°-60°	1.1	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1515.7	96.2
0°-40°	1564.0	99.3
0°-60°	1574.5	100.0
0°-90°	1575.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1575.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5715	
5°	5619	514
15°	3023	797
25°	375	205
35°	72	48
45°	12	9
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270158

CATALOG NUMBER: P3A17R309740DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5714.7
1°	5710.4
2°	5696.9
3°	5681.7
4°	5659.0
5°	5618.7
6°	5553.3
7°	5444.4
8°	5295.9
9°	5102.1
10°	4849.6
11°	4549.4
12°	4221.7
13°	3844.4
14°	3449.5
15°	3023.3
16°	2605.8
17°	2203.5
18°	1817.7
19°	1463.7
20°	1165.3
21°	917.1
22°	721.4
23°	571.0
24°	457.3
25°	375.4
26°	313.0
27°	266.0
28°	229.9
29°	196.9
30°	166.9
32.5°	105.2
35°	71.5
37.5°	44.6
40°	25.7
42.5°	17.1
45°	11.6
47.5°	6.7
50°	3.1
52.5°	1.2
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P1270158
CATALOG NUMBER: P3A17R309740DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)