

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270197

Luminaire Tested: P3A17R359740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R359740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 495.0 lumens
Efficiency: N/A
Efficacy: 23.3 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270197

CATALOG NUMBER: P3A17R359740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270197

CATALOG NUMBER: P3A17R359740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113083
5°	110675
10°	103650
15°	93031
20°	80927
25°	68956
30°	57781
35°	46016
40°	33262
45°	21056
50°	11462
55°	7952
60°	7499
65°	7005
70°	6668
75°	5676
80°	5430
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21056 cd/sqm

TEST NUMBER: P1270197

CATALOG NUMBER: P3A17R359740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	9.5
10°-20°	114.0	23.0
20°-30°	130.7	26.4
30°-40°	106.6	21.5
40°-50°	53.8	10.9
50°-60°	20.0	4.0
60°-70°	13.4	2.7
70°-80°	7.4	1.5
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.5	58.9
0°-40°	398.2	80.4
0°-60°	471.9	95.3
0°-90°	495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	495.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	516	
5°	503	47
15°	410	114
25°	285	131
35°	172	107
45°	68	54
55°	21	20
65°	14	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1270197

CATALOG NUMBER: P3A17R359740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	515.7
1°	515.0
2°	513.8
3°	511.4
4°	507.7
5°	502.8
6°	496.7
7°	490.6
8°	482.6
9°	474.7
10°	465.5
11°	455.7
12°	445.3
13°	433.7
14°	421.5
15°	409.8
17.5°	378.6
20°	346.8
22.5°	314.4
25°	285.0
27.5°	256.3
30°	228.2
32.5°	200.0
35°	171.9
37.5°	143.7
40°	116.2
42.5°	90.5
45°	67.9
47.5°	48.9
50°	33.6
52.5°	24.5
55°	20.8
57.5°	19.0
60°	17.1
62.5°	15.3
65°	13.5
67.5°	11.6
70°	10.4
72.5°	8.6
75°	6.7
77.5°	5.5
80°	4.3
82.5°	3.1
85°	1.8
87.5°	1.2



TEST NUMBER: P1270197

CATALOG NUMBER: P3A17R359740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)