

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270326

Luminaire Tested: P3A17R609740DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1270326  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R609740DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1612.9 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270326

CATALOG NUMBER: P3A17R609740DE010 E3CB1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1270326

CATALOG NUMBER: P3A17R609740DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98  | 97  | 96  | 95  | 94  |    |    |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 93  | 91  | 89  | 87  |    |    |
| 3   | 103 | 96  | 91  | 88  | 101 | 95  | 90  | 87  | 92  | 89  | 85  | 90  | 87  | 84  | 88  | 85  | 83  | 81  |    |    |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 76  |    |    |
| 5   | 93  | 84  | 79  | 74  | 91  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 76  | 73  | 79  | 75  | 72  | 71  |    |    |
| 6   | 88  | 79  | 73  | 69  | 87  | 79  | 73  | 69  | 77  | 72  | 68  | 76  | 71  | 68  | 74  | 70  | 68  | 66  |    |    |
| 7   | 84  | 75  | 69  | 64  | 82  | 74  | 68  | 64  | 73  | 68  | 64  | 71  | 67  | 64  | 70  | 66  | 63  | 62  |    |    |
| 8   | 80  | 70  | 64  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 59  | 58  |    |    |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 63  | 59  | 56  | 55  |    |    |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 56  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 385167 |
| 5°  | 369887 |
| 10° | 380844 |
| 15° | 385746 |
| 20° | 340603 |
| 25° | 287049 |
| 30° | 232795 |
| 35° | 151621 |
| 40° | 69645  |
| 45° | 26700  |
| 50° | 8938   |
| 55° | 2370   |
| 60° | 2193   |
| 65° | 1920   |
| 70° | 1603   |
| 75° | 2118   |
| 80° | 1515   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26700 cd/sqm

TEST NUMBER: P1270326

CATALOG NUMBER: P3A17R609740DE010 E3CB1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 161.7  | 10.0      |
| 10°-20°   | 465.3  | 28.8      |
| 20°-30°   | 542.7  | 33.6      |
| 30°-40°   | 350.2  | 21.7      |
| 40°-50°   | 78.5   | 4.9       |
| 50°-60°   | 7.8    | 0.5       |
| 60°-70°   | 3.7    | 0.2       |
| 70°-80°   | 2.1    | 0.1       |
| 80°-90°   | 0.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1169.8 | 72.5      |
| 0°-40°    | 1520.0 | 94.2      |
| 0°-60°    | 1606.3 | 99.6      |
| 0°-90°    | 1612.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1612.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1756 |      |
| 5°  | 1680 | 162  |
| 15° | 1699 | 465  |
| 25° | 1186 | 543  |
| 35° | 566  | 350  |
| 45° | 86   | 78   |
| 55° | 6    | 8    |
| 65° | 4    | 4    |
| 75° | 2    | 2    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1270326

CATALOG NUMBER: P3A17R609740DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1756.5 |
| 2.5°  | 1727.8 |
| 5°    | 1680.4 |
| 7.5°  | 1677.9 |
| 10°   | 1710.4 |
| 12.5° | 1731.6 |
| 15°   | 1699.2 |
| 17.5° | 1601.8 |
| 20°   | 1459.6 |
| 22.5° | 1311.2 |
| 25°   | 1186.4 |
| 27.5° | 1064.2 |
| 30°   | 919.4  |
| 32.5° | 749.8  |
| 35°   | 566.4  |
| 37.5° | 386.7  |
| 40°   | 243.3  |
| 42.5° | 146.0  |
| 45°   | 86.1   |
| 47.5° | 49.9   |
| 50°   | 26.2   |
| 52.5° | 8.7    |
| 55°   | 6.2    |
| 57.5° | 5.0    |
| 60°   | 5.0    |
| 62.5° | 3.7    |
| 65°   | 3.7    |
| 67.5° | 3.7    |
| 70°   | 2.5    |
| 72.5° | 2.5    |
| 75°   | 2.5    |
| 77.5° | 1.2    |
| 80°   | 1.2    |
| 82.5° | 1.2    |
| 85°   | 1.2    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)