

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270333

Luminaire Tested: P3A17R609740DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1270333  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R609740DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1495.0 lumens  
Efficiency: N/A  
Efficacy: 70.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270333  
CATALOG NUMBER: P3A17R609740DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1270333  
 CATALOG NUMBER: P3A17R609740DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	391701
5°	369777
10°	360180
15°	351943
20°	327232
25°	292517
30°	223452
35°	129001
40°	50065
45°	20870
50°	4605
55°	688
60°	526
65°	311
70°	385
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20870 cd/sqm



TEST NUMBER: P1270333  
 CATALOG NUMBER: P3A17R609740DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.6	10.6
10°-20°	431.8	28.9
20°-30°	540.9	36.2
30°-40°	302.4	20.2
40°-50°	57.5	3.8
50°-60°	2.9	0.2
60°-70°	0.7	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1131.3	75.7
0°-40°	1433.7	95.9
0°-60°	1494.1	99.9
0°-90°	1495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1495.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1786	
5°	1680	159
15°	1550	432
25°	1209	541
35°	482	302
45°	67	57
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1270333  
CATALOG NUMBER: P3A17R609740DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1786.3
1°	1779.0
2°	1755.8
3°	1728.2
4°	1702.6
5°	1679.9
6°	1662.8
7°	1648.1
8°	1637.1
9°	1626.7
10°	1617.6
11°	1608.4
12°	1598.0
13°	1585.1
14°	1569.9
15°	1550.3
16°	1526.4
17°	1499.5
18°	1468.9
19°	1434.1
20°	1402.3
21°	1368.0
22°	1332.6
23°	1295.3
24°	1254.3
25°	1209.0
26°	1155.8
27°	1096.5
28°	1029.9
29°	958.9
30°	882.5
31°	805.4
32°	725.9
32.5°	682.5
33°	643.4
34°	562.0
35°	481.9
36°	409.7
37°	333.3
37.5°	298.4
38°	264.2
39°	212.8
40°	174.9
42.5°	106.4
45°	67.3



TEST NUMBER: P1270333  
CATALOG NUMBER: P3A17R609740DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	37.3
50°	13.5
52.5°	3.1
55°	1.8
57.5°	1.2
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)