

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426770

Luminaire Tested: P3A17RH9740DE010 E3HY1GPH

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426770
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17RH9740DE010 E3HY1GPH
Description: 3in Adjustable LED luminaire with, RH optic, 4000K CCT AND, 97CRI , E3HY1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 445.0 lumens
Efficiency: N/A
Efficacy: 21.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426770

CATALOG NUMBER: P3A17RH9740DE010 E3HY1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1426770

CATALOG NUMBER: P3A17RH9740DE010 E3HY1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	98	95	105	101	97	95	98	95	93		96	94	92		94
4	103	98	94	90	102	97	93	90	95	91	89		93	90	88		91
5	100	94	89	86	99	93	89	86	91	88	85		90	87	84		88
6	97	90	86	83	96	89	85	82	88	84	82		87	84	81		86
7	94	87	82	79	93	86	82	79	85	81	79		84	81	78		83
8	91	84	79	76	90	83	79	76	82	79	76		81	78	76		81
9	88	81	77	74	87	81	76	74	80	76	73		79	76	73		78
10	85	78	74	71	85	78	74	71	77	73	71		77	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302147
5°	275830
10°	238985
15°	210240
20°	91451
25°	35034
30°	23700
35°	8031
40°	2490
45°	775
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 775 cd/sqm

TEST NUMBER: P1426770

CATALOG NUMBER: P3A17RH9740DE010 E3HY1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.6	25.5
10°-20°	228.0	51.2
20°-30°	77.3	17.4
30°-40°	23.6	5.3
40°-50°	2.4	0.5
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.9	94.1
0°-40°	442.6	99.5
0°-60°	445.0	100.0
0°-90°	445.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	445.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1378	
5°	1253	114
15°	926	228
25°	145	77
35°	30	24
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426770

CATALOG NUMBER: P3A17RH9740DE010 E3HY1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1377.9
2.5°	1347.9
5°	1253.1
7.5°	1148.2
10°	1073.3
12.5°	1005.9
15°	926.1
17.5°	687.7
20°	391.9
22.5°	191.0
25°	144.8
27.5°	117.3
30°	93.6
32.5°	59.9
35°	30.0
37.5°	16.2
40°	8.7
42.5°	5.0
45°	2.5
47.5°	1.2
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)